



Eaton 235453

Eaton Moeller series xPole - PFIM Type AC, A, U, R RCCB. Residual current circuit breaker (RCCB), 40A, 4p, 30mA, type G

□□□□

| | |
|-----------------------------|---------------------------------------------------------|
| PRODUCT NAME | Eaton Moeller series xPole - PFIM Type AC, A, U, R RCCB |
| CATALOG NUMBER | 235453 |
| PRODUCT LENGTH/DEPTH | 76 mm |
| PRODUCT HEIGHT | 80 mm |
| PRODUCT WIDTH | 70 mm |
| PRODUCT WEIGHT | 0.362 kg |
| COMPLIANCES | RoHS conform |
| CERTIFICATIONS | IEC/EN 61008 |



Powering Business Worldwide

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| USED WITH | KLV-TC-4 276241 (Compact enclosure) Z-FW/LP 248296 (Remote control and automatic switching device) Z-RC/AK-4MU 101062 (sealing cover set) |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|------------------------|------|
| AMPERAGE RATING | 40 A |
|------------------------|------|

| | |
|-----------------------|---------------------|
| VOLTAGE RATING | 230 V AC / 400 V AC |
|-----------------------|---------------------|

| | |
|-----------------|-------------------------------------------------------------------|
| FEATURES | Additional equipment possible Residual current circuit breaker |
|-----------------|-------------------------------------------------------------------|

| | |
|-----------------------------|-------------|
| ACCESSORIES REQUIRED | Z-HK 248432 |
|-----------------------------|-------------|

| | |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| 10.10 TEMPERATURE RISE | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------|

| | |
|-----------------------------------|------------------------------------------------------------------------------------------------|
| 10.11 SHORT-CIRCUIT RATING | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
|-----------------------------------|------------------------------------------------------------------------------------------------|

| | |
|--------------------------------------------|------------------------------------------------------------------------------------------------|
| 10.12 ELECTROMAGNETIC COMPATIBILITY | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
|--------------------------------------------|------------------------------------------------------------------------------------------------|

| | |
|----------------------------------|----------------------------------------------------------------------------------------------------------|
| 10.13 MECHANICAL FUNCTION | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |
|----------------------------------|----------------------------------------------------------------------------------------------------------|

| | |
|------------------------------------|--------------------------------------------|
| 10.2.2 CORROSION RESISTANCE | Meets the product standard's requirements. |
|------------------------------------|--------------------------------------------|

| | |
|-----------------------------------------------------------------|--------------------------------------------|
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES | Meets the product standard's requirements. |
|-----------------------------------------------------------------|--------------------------------------------|

| | |
|-----------------------------------------------------------------------------------|--------------------------------------------|
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT | Meets the product standard's requirements. |
|-----------------------------------------------------------------------------------|--------------------------------------------|

| | |
|-----------------------------------------------------------------------------------------|--------------------------------------------|
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements. |
|-----------------------------------------------------------------------------------------|--------------------------------------------|

| | |
|---------------------------------------------------------|--------------------------------------------|
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION | Meets the product standard's requirements. |
|---------------------------------------------------------|--------------------------------------------|

| | |
|-------|----------------------------------------------------------------------|
| □□□□□ | eaton-rccb-rcbo-g9-il019140zu.pdf |
| □□□□ | eaton-xpole-pfim-x-rccb-catalog-ca019029en-en-us.pdf |

| | |
|-----------------------------------------------------------------|----------------------------------------------------------------------------------|
| 10.2.5 LIFTING | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 MECHANICAL IMPACT | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 INSCRIPTIONS | Meets the product standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| FITTED WITH: | Interlocking device |
| FRAME | 45 mm |
| FREQUENCY RATING | 50 Hz |
| POLLUTION DEGREE | 2 |
| LIFESPAN, MECHANICAL | 20000 operations |
| MOUNTING METHOD | Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715 DIN rail |
| CLIMATIC PROOFING | 25-55 °C / 90-95% relative humidity according to IEC 60068-2 |
| EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT | 13.1 W |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) | 4 kV |
| RATED SHORT-TIME | 10 kA |

| | |
|----------------------------------------------------------------|------------------------------------------------|
| WITHSTAND CURRENT (ICW) | |
| ADMISSIBLE BACK-UP FUSE OVERLOAD - MAX | 25 A gG/gL |
| BUILT-IN WIDTH (NUMBER OF UNITS) | 70 mm (4 SU) |
| BUSBAR MATERIAL THICKNESS | 0.8 mm - 2 mm |
| SHORT-CIRCUIT RATING | 63 A (max. admissible back-up fuse) |
| TERMINAL PROTECTION | Finger and hand touch safe, DGUV VS3, EN 50274 |
| TERMINALS (TOP AND BOTTOM) | Open mouthed/lift terminals |
| TEST CIRCUIT RANGE | 196 V AC - 264 V AC |
| AMBIENT OPERATING TEMPERATURE - MAX | 60 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -25 °C |
| BUILT-IN DEPTH | 70.5 mm |
| CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX | 16 mm ² |
| CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN | 1.5 mm ² |
| CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX | 35 mm ² |
| CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN | 1.5 mm ² |
| FAULT CURRENT RATING | 30 mA |
| HEAT DISSIPATION CAPACITY | 0 W |
| HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT | 0 W |
| PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MAX | 60 °C |
| PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MIN | -35 °C |
| DEGREE OF PROTECTION | IP20 IP20, IP40 with suitable enclosure |

| | |
|----------------------------------|-------------------|
| IMPULSE WITHSTAND CURRENT | Surge-proof, 3 kA |
| NUMBER OF POLES | Four-pole |
| LEAKAGE CURRENT TYPE | AC |
| LIFESPAN, ELECTRICAL | 4000 operations |

| | |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------|
| TYPE | <ul style="list-style-type: none"> • PFIM • Residual current circuit breakers • Type G (ÖVE E 8601) |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------|

| | |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SPECIAL FEATURES | <ul style="list-style-type: none"> • Maximum operating temperature is 60 °C: Starting at 40 °C, the max. permissible continuous current decreases by 2.5% for every 1 °C • Tripping signal contact for subsequent installation Z-NHK 248434 |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| APPLICATION | <ul style="list-style-type: none"> • 3-phase application without N (400V AC phase-phase) not allowed • Residual current circuit breaker for residential and commercial applications • xPole - Switchgear for residential and commercial applications |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|----------------------------------------------------------------------|-----------------------------|
| FUNCTIONS | Short-time delayed tripping |
| SENSITIVITY TYPE | AC current sensitive |
| RATED FAULT CURRENT - MAX | 0.03 A |
| RATED FAULT CURRENT - MIN | 0.03 A |
| RATED INSULATION VOLTAGE (UI) | 440 V |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 40 A |
| RATED OPERATIONAL | 400 V |

