

Eaton 239451

Eaton Moeller® series DILM Contactor, 380 V 400 V 37 kW, 2 N/O, 2 NC, 400 V 50 Hz, 440 V 60 Hz, AC operation, Screw terminals

PRODUCT NAME	Eaton Moeller® series DILM contactor
CATALOG NUMBER	239451
PRODUCT LENGTH/DEPTH	175 mm
PRODUCT HEIGHT	170 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	2.22 kg
CERTIFICATIONS	VDE 0660 CSA UL IEC/EN 60947
CATALOG NOTES	Contacts according to EN 50012

**ELECTRICAL
CONNECTION TYPE FOR
AUXILIARY- AND
CONTROL-CURRENT
CIRCUIT**

Screw connection

NUMBER OF POLES

Three-pole

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**10.11 SHORT-CIRCUIT
RATING**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.12 ELECTROMAGNETIC
COMPATIBILITY**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.13 MECHANICAL
FUNCTION**

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION
RESISTANCE**

Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF
THERMAL STABILITY OF
ENCLOSURES**

Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF
RESISTANCE OF
INSULATING MATERIALS
TO NORMAL HEAT**

Meets the product standard's requirements.

**10.2.3.3 RESIST. OF
INSUL. MAT. TO
ABNORMAL HEAT/FIRE
BY INTERNAL ELECT.
EFFECTS**

Meets the product standard's requirements.

**10.2.4 RESISTANCE TO
ULTRA-VIOLET (UV)
RADIATION**

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

**10.2.6 MECHANICAL
IMPACT**

Does not apply, since the entire switchgear needs to be evaluated.

CHARACTERISTIC CURVE

[eaton-contactors-switch-dilm-characteristic-curve.eps](#)

[eaton-contactors-switch-dilm-characteristic-curve-002.eps](#)

**DECLARATIONS OF
CONFORMITY**

[eaton-contactor-declaration-of-conformity-uk251234en.pdf](#)

MCAD MODEL

[dil_m80_150_22.stp](#)

[dil_m80_150_22.dwg](#)

[eaton-dil-contactors-instruction-leaflet-il03407039z.pdf](#)

[eaton-contactors-dilm-dimensions-003.eps](#)

[eaton-contactors-dilm-3d-drawing.eps](#)

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Mirror contact
OPERATING FREQUENCY	3600 mechanical Operations/h (AC operated)
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8000 V AC
UTILIZATION CATEGORY	AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-3: Normal AC induction motors: starting, switch off during running
CONNECTION	Screw terminals
AMBIENT OPERATING TEMPERATURE - MAX	60 °C

AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)	200 A
CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)	80 A
CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)	94 A
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)	225 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	9 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	3 W
APPLICATION	Contactors for Motors
PRODUCT CATEGORY	Contactors
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
ARCING TIME	15 ms
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
SCREWDRIVER SIZE	0.8 x 5.5/1 x 6 mm, Terminal screw, Control circuit cables, Standard screwdriver 2, Terminal screw, Control circuit cables, Pozidriv

	screwdriver
VOLTAGE TYPE	AC
DEGREE OF PROTECTION	IP00
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)	3
RATED BREAKING CAPACITY AT 220/230 V	800 A
RATED BREAKING CAPACITY AT 380/400 V	800 A
RATED BREAKING CAPACITY AT 500 V	800 A
RATED BREAKING CAPACITY AT 660/690 V	650 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	400 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	400 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	440 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	440 V
DROP-OUT VOLTAGE	AC operated: 0.6 - 0.3 x UC, AC operated
OVERVOLTAGE CATEGORY	III
DUTY FACTOR	100 %
EMITTED INTERFERENCE	According to EN 60947-1
INTERFERENCE	According to EN 60947-1

IMMUNITY	
LIFESPAN, MECHANICAL	10,000,000 Operations (AC operated)
PICK-UP VOLTAGE	0.8 - 1.1 V AC x Uc
POWER CONSUMPTION, PICK-UP, 50 HZ	310 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz
SAFE ISOLATION	690 V AC, Between the contacts, According to EN 61140 690 V AC, Between coil and contacts, According to EN 61140
POWER CONSUMPTION, PICK-UP, 60 HZ	345 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz
RESIDUAL CURRENT	1 mA (with actuation of A1 - A2 by the electronics with "0" signal)
SCREW SIZE	M3.5, Terminal screw, Control circuit cables M10, Terminal screw, Main cables 5 mm AF, Hexagon socket-head spanner, Terminal screw, Main cables
POWER CONSUMPTION, SEALING, 50 HZ	26 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz 5.8 W, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz
POWER CONSUMPTION, SEALING, 60 HZ	30 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz 5.8 W, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz
TERMINAL CAPACITY (STRANDED)	1 x (16 - 70) mm ² , Main cables 2 x (16 - 50) mm ² , Main cables
TERMINAL CAPACITY (COPPER BAND)	2 x (6 x 16 x 0.8) mm (Number of segments x width x thickness), Main cables
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	2 x (10 - 50) mm ² , Main cables 1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables

	1 x (10 - 70) mm ² , Main cables
SHOCK RESISTANCE	<p>7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms</p> <p>10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms</p> <p>10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms</p> <p>5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms</p> <p>5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms</p> <p>7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms</p>
TERMINAL CAPACITY (SOLID)	<p>2 x (0.75 - 2.5) mm², Control circuit cables</p> <p>1 x (0.75 - 2.5) mm², Control circuit cables</p>
TERMINAL CAPACITY (SOLID/STRANDED AWG)	<p>18 - 14, Control circuit cables</p> <p>Single 8...3/0, double 8...2/0, Main cables</p>
TIGHTENING TORQUE	<p>14 Nm, Screw terminals, Main cables</p> <p>1.2 Nm, Screw terminals, Control circuit cables</p>
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED INSULATION VOLTAGE (UI)	690 V
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947)	1120 A

RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V	110 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	65 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V	27 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V	110 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V	70 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V	110 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	80 A
RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ	27.5 kW
RATED OPERATIONAL POWER AT AC-3, 380/400	37 kW

V, 50 HZ	
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	48 kW
RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ	11.5 kW
RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ	13 kW
RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ	20 kW
RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ	24 kW
RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ	25 kW
RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ	29 kW
RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ	26 kW
RATED OPERATIONAL POWER (NEMA)	44.7 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RESISTANCE PER POLE	0.6 mΩ
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	5.8 W
STRIPPING LENGTH (CONTROL CIRCUIT CABLE)	10 mm
STRIPPING LENGTH (MAIN CABLE)	24 mm
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	20 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN	14 ms
SWITCHING TIME (AC OPERATED, MAKE	14 ms

CONTACTS, OPENING DELAY) - MAX	
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN	9 ms
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	10 kA, 600 A max. fuse, SCCR (UL/CSA) 10 kA, 600 A max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)	100 kA, 300 A CLASS J max. fuse, SCCR (UL/CSA) 30 kA, 600 A max. fuse, SCCR (UL/CSA) 65 kA, 250 A max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)	100 kA, 300 A CLASS J max. fuse, SCCR (UL/CSA) 30 kA, 600 A max. fuse, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V	250 A gG/gL
SUITABLE FOR	Also motors with efficiency class IE3
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V	200 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V	160 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V	160 A gG/gL
CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)	110 A
CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)	98 A
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	90 A
RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ	51 kW
RATED OPERATIONAL	58 kW

POWER AT AC-3, 500 V, 50 HZ	
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	63 kW
ACTUATING VOLTAGE	400 V 50 Hz, 440 V 60 Hz
ALTITUDE	Max. 2000 m
OPERATING VOLTAGE AT AC, 50 HZ - MIN	230 V
OPERATING VOLTAGE AT AC, 50 HZ - MAX	690 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	230 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	690 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

