

Eaton 230113

Eaton Moeller® series DILM Replacement coil, Tool-less plug connection, RAC 440: 380 - 440 V 50/60 Hz, AC, For use with: DILM115, DILM150, DILM170

PRODUCT NAME	Eaton Moeller® series DILM replacement coil
CATALOG NUMBER	230113
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	110 mm
PRODUCT WIDTH	63.2 mm
PRODUCT WEIGHT	0.245 kg
CERTIFICATIONS	UL CE CSA File No.: 012528 UL 508 CSA-C22.2 No. 14-05 CSA Class No.: 2411-03, 3211-04 UL File No.: E29096 IEC/EN 60947-4-1 CSA UL Category Control No.: NLDX

ACCESSORIES	
Individual coils	
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.



[IL03407042Z](#)

10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
VOLTAGE TYPE	AC
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	440 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	380 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	440 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	380 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
PRODUCT CATEGORY	Accessories

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

