



Eaton 235922

Eaton Moeller series xPole - PFDM RCCB, PFDM-125/4/03-A. Residual current circuit-breaker, 125A, 4p, 3mA, A-Char

□□□□

PRODUCT NAME	Eaton Moeller series xPole - PFDM RCCB
CATALOG NUMBER	235922
PRODUCT LENGTH/DEPTH	88 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	71 mm
PRODUCT WEIGHT	0.41 kg
COMPLIANCES	RoHS conform CE Marked

□□□□	
AMPERAGE RATING	125 A
FEATURES	Additional equipment possible
FREQUENCY RATING	50 Hz
MOUNTING METHOD	DIN rail
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	33.6 W
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	10 kA
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	71.5 mm
FAULT CURRENT RATING	300 mA
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
DEGREE OF PROTECTION	IP20
NUMBER OF POLES	Four-pole
LEAKAGE CURRENT TYPE	A
SPECIAL FEATURES	Maximum operating temperature is 60 °C: Starting at 40 °C, the max. permissible continuous current decreases by 2.2% for every 1 °C
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	125 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
SURGE CURRENT CAPACITY	0.2 kA
WIDTH IN NUMBER OF MODULAR SPACINGS	4

□□	
□□□	eaton-frcm-wiring-diagram.jpg
□□□□	eaton-protective-devices-catalog-ca20190603-en-us.pdf
□□	eaton-frcm-dimensions.jpg

