

Eaton 242517

Eaton Moeller series xPole - PLS6/M MCB.
PLSM, 3-pole+N, tripping characteristic: B,
rated current In: 16 A, rated switching
capacity IEC/EN 60898-1: 10 kA

PRODUCT NAME	Eaton Moeller series xPole - PLS6/M MCB
CATALOG NUMBER	242517
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	70 mm
PRODUCT WEIGHT	0.399 kg
COMPLIANCES	RoHS conform

USED WITH	PLSM Miniature circuit breaker
AMPERAGE RATING	16 A
FEATURES	Concurrently switching N-neutral Additional equipment possible
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

CHARACTERISTIC CURVE	eaton-xpole-mmc4-6-m-mcb-characteristic-curve.jpg
DECLARATIONS OF CONFORMITY	DA-DC-03_PLS
	eaton-xpole-mmc4-6-m-mcb-wiring-diagram-004.jpg
	eaton-xpole-mmc4-6-m-mcb-dimensions.jpg eaton-xpole-mmc4-6-m-mcb-3d-drawing-006.jpg

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	7.2 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
TRIPPING CHARACTERISTIC	B
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE	1 mm ²

CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
WIDTH IN NUMBER OF MODULAR SPACINGS	4
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Three-pole + N
RELEASE CHARACTERISTIC	B
TYPE	<ul style="list-style-type: none"> • Miniature circuit breaker • PLSM
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	<ul style="list-style-type: none"> • Switchgear for residential and commercial applications • xPole - Switchgear for residential and commercial applications
NUMBER OF POLES (PROTECTED)	3

NUMBER OF POLES (TOTAL)	4
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	16 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 400 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 230 V	0 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 400 V	0 kA
RATED SWITCHING CAPACITY (IEC/EN 60898- 1)	10 kA
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT	0 W
POWER LOSS	7.5 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

