



## Eaton 242575

Eaton Moeller series xPole - PLS6/M MCB.  
PLSM, 4 pole, tripping characteristic: B, rated  
current In: 2.5 A, rated switching capacity  
IEC/EN 60898-1: 10 kA

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - PLS6/M MCB
<b>CATALOG NUMBER</b>	242575
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	70 mm
<b>PRODUCT WEIGHT</b>	0.458 kg
<b>COMPLIANCES</b>	RoHS conform



*Powering Business Worldwide*

<b>USED WITH</b>	Miniature circuit breaker PLSM
<b>AMPERAGE RATING</b>	2.5 A
<b>FEATURES</b>	Additional equipment possible
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF</b>	Does not apply, since the

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-xpole-mmc4-6-m- mcb-characteristic- curve.jpg</a>
<b>PEP ECO-PASSPORT</b>	<a href="#">eaton-non-selective- universal-mcb-pep-eato- 00046-v0102-en.pdf</a>
□□□□□	<a href="#">eaton-rccb-rcbo-g9- il019140zu.pdf</a>
□□□	<a href="#">eaton-xpole-mmc4-6-m- mcb-wiring-diagram- 006.jpg</a>
□□	<a href="#">eaton-xpole-mmc4-6-m- mcb-dimensions.jpg</a>  <a href="#">eaton-xpole-mmc4-6-m- mcb-3d-drawing-006.jpg</a>

<b>PROTECTION OF ASSEMBLIES</b>	entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	2
<b>DEGREE OF PROTECTION</b>	IP20
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	6 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>TRIPPING CHARACTERISTIC</b>	B
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE</b>	1 mm <sup>2</sup>

<b>CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	
<b>CURRENT LIMITING CLASS</b>	3
<b>FREQUENCY RATING - MAX</b>	60 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	4
<b>VOLTAGE TYPE</b>	AC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Four-pole
<b>RELEASE CHARACTERISTIC</b>	B
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Miniature circuit breaker</li> <li>• PLSM</li> </ul>
<b>SPECIAL FEATURES</b>	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole - Switchgear for residential and commercial applications</li> </ul>
<b>NUMBER OF POLES (PROTECTED)</b>	4
<b>NUMBER OF POLES (TOTAL)</b>	4
<b>RATED INSULATION VOLTAGE (UI)</b>	440 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	2.5 A
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	400 V
<b>RATED SHORT-CIRCUIT</b>	10 kA

