



□□□□

## Eaton 242681

Eaton Moeller series xPole - PLS6/M MCB.  
PLS6, 1-pole, tripping characteristic: C, rated  
current In: 16 A, rated switching capacity  
IEC/EN 60898-1: 6 kA

□□□□

|                                 |  |
|---------------------------------|--|
| <b>PRODUCT NAME</b>             | Eaton Moeller series xPole<br>- PLS6/M MCB |
| <b>CATALOG NUMBER</b>           | 242681                                     |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 85 mm                                      |
| <b>PRODUCT HEIGHT</b>           | 73 mm                                      |
| <b>PRODUCT WIDTH</b>            | 17.5 mm                                    |
| <b>PRODUCT WEIGHT</b>           | 0.12 kg                                    |
| <b>COMPLIANCES</b>              | RoHS conform                               |
| <b>CERTIFICATIONS</b>           | CE   |



Powering Business Worldwide

|   |  |
|---|--|
| <b>USED WITH</b>  | Miniature circuit breaker PLS6   |
| <b>AMPERAGE RATING</b>  | 16 A   |
| <b>FEATURES</b>   | Additional equipment possible  |
| <b>10.10 TEMPERATURE RISE</b>   | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>   | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>  | Meets the product standard's requirements.   |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.   |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.   |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.   |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | Meets the product standard's requirements.   |
| <b>10.2.5 LIFTING</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.2.6 MECHANICAL IMPACT</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.2.7 INSCRIPTIONS</b>  | Meets the product standard's requirements.   |
| <b>10.3 DEGREE OF</b>   | Does not apply, since the  |

|                             |  |
|-----------------------------|--|
| <b>CHARACTERISTIC CURVE</b> | <a href="#">eaton-xpole-mmc4-6-m-mcb-characteristic-curve-002.jpg</a>  |
| <b>PEP ECO-PASSPORT</b>     | <a href="#">eaton-non-selective-universal-mcb-pep-eato-00046-v0102-en.pdf</a>  |
| □□□□□                       | <a href="#">eaton-mcb-rccb-rcbo-g9-il019140zu.pdf</a>  |
| □□□                         | <a href="#">eaton-xpole-mmc4-6-m-mcb-wiring-diagram-002.jpg</a>  |
| □□                          | <a href="#">eaton-xpole-mmc4-6-m-mcb-dimensions.jpg</a><br><a href="#">eaton-xpole-mmc4-6-m-mcb-3d-drawing-004.jpg</a> |

|   |  |
|---|--|
| <b>PROTECTION OF ASSEMBLIES</b>                                 | entire switchgear needs to be evaluated.                           |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                         |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                             |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                             |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                             |
| <b>POLLUTION DEGREE</b>   | 2  |
| <b>DEGREE OF PROTECTION</b>                                     | IP20   |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 2.2 W  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 4 kV   |
| <b>TRIPPING CHARACTERISTIC</b>                                  | C  |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 75 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C   |
| <b>BUILT-IN DEPTH</b>   | 70.5 mm  |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>  | 25 mm <sup>2</sup>   |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>  | 1 mm <sup>2</sup>  |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>   | 25 mm <sup>2</sup>   |
| <b>CONNECTABLE</b>  | 1 mm <sup>2</sup>  |

|  |  |
|--|--|
| <b>CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>                    |  |
| <b>CURRENT LIMITING CLASS</b>  | 3  |
| <b>FREQUENCY RATING - MAX</b>  | 60 Hz  |
| <b>FREQUENCY RATING - MIN</b>  | 50 Hz  |
| <b>HEAT DISSIPATION CAPACITY</b>                                     | 0 W  |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>                  | 0 W  |
| <b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>                           | 1  |
| <b>VOLTAGE TYPE</b>  | AC   |
| <b>OVERVOLTAGE CATEGORY</b>  | III  |
| <b>NUMBER OF POLES</b>   | Single-pole  |
| <b>RELEASE CHARACTERISTIC</b>  | C  |
| <b>TYPE</b>  | <ul style="list-style-type: none"> <li>• Miniature circuit breaker</li> <li>• PLS6</li> </ul>  |
| <b>SPECIAL FEATURES</b>  | Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity  |
| <b>APPLICATION</b>   | <ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole - Switchgear for residential and commercial applications</li> </ul> |
| <b>NUMBER OF POLES (PROTECTED)</b>                                   | 1  |
| <b>NUMBER OF POLES (TOTAL)</b>                                       | 1  |
| <b>RATED INSULATION VOLTAGE (UI)</b>                                 | 440 V  |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 16 A   |
| <b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>                          | 230 V  |
| <b>RATED SHORT-CIRCUIT</b>   | 6 kA   |

