



□□□□□

Eaton 239127

FAZ6-C3/3. Miniature circuit breaker (MCB),
3 A, 3p, characteristic: C, 6 kA

□□□□

PRODUCT NAME	Eaton Moeller series xEffect - FAZ6 MCB
CATALOG NUMBER	239127
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	53.1 mm
PRODUCT WEIGHT	0.36 kg
COMPLIANCES	RoHS conform

0000

AMPERAGE RATING

3 A

FEATURES

Additional equipment possible

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF PROTECTION OF ASSEMBLIES

Does not apply, since the entire switchgear needs to be evaluated.

00

CHARACTERISTIC CURVE

[eaton-xeffect-faz6-mcb-characteristic-curve.jpg](#)

[eaton-xeffect-faz6-mcb-characteristic-curve-002.jpg](#)

000

[eaton-xpole-mmc4-6-mcb-wiring-diagram-005.jpg](#)

0000

[eaton-xeffect-faz-mcb-catalog-ca003028en-en-us.pdf](#)

00

[eaton-xeffect-faz-mcb-dimensions-003.jpg](#)

[eaton-xeffect-faz6-mcb-3d-drawing-002.jpg](#)

[eaton-xeffect-faz6-mcb-3d-drawing-005.jpg](#)

000000

[eaton-maximum-cable-lengths-for-eatons-protective-devices-brochure-br034006en-en-us.pdf](#)

10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	3.6 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3

FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE RATING (IEC/EN 60898-1)	415 V
WIDTH IN NUMBER OF MODULAR SPACINGS	3
VOLTAGE RATING (IEC/EN 60947-2)	400
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
RELEASE CHARACTERISTIC	C
NUMBER OF POLES (PROTECTED)	3
NUMBER OF POLES (TOTAL)	3
OPERATIONAL VOLTAGE (IEC/EN 60947-2) - MAX	400 V
OPERATIONAL VOLTAGE AT DC (EC/EN 60947-2) - MAX	60 V
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	3 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	230 V
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICS	6 kA
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60947-2) - ICS	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	10 kA
RATED SHORT-CIRCUIT	10 kA

BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V	
RATED SWITCHING CAPACITY (IEC/EN 60947-2)	7.5 kA
POWER LOSS	3.6 W
