

Eaton 250NHG1BI

Eaton Bussmann series low voltage NH Fuse, 500V, 250A, 120 kAIC, Combination fuse status indicator, fuse, Class C gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	250NHG1BI
UPC	051712233309
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	63 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	407.3333333 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	250 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH1
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-1 Solid link FEH- Fuse extraction handle SD12-SK Shroud kit SD00-PB 2-phase barriers TD1-IP20 Triple pole protection kit
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
CONNECTION	Blade end
CONSTRUCTION	NH1
CONSTRUCTION SIZE	NH1
FUSE SHAPE	Knife blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	SD1-D Single pole NH Fuse base Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD1-D Triple pole NH Fuse base
MATERIAL	Ceramic body



QUANTITY	3
VOLTAGE RATING	500 V
TYPE	fuse
APPLICATION	• industrial • Utilities, Solar, Wind

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

