

Eaton 248301

Eaton Distribution parts. Remote testing module, max. 400V-AC, 0.5A, 0.5HP

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	248301
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	65.5 mm
PRODUCT WIDTH	8.8 mm
PRODUCT WEIGHT	0.04 kg
COMPLIANCES	RoHS conform

USED WITH	Remote testing module Accessory for residual current circuit breaker Accessory
ACCESSORY/SPARE PART TYPE	Remote test module
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	0.02 W
MOUNTING METHOD	For fitting on left to: FI
ADDITIONAL EQUIPMENT REQUIRED	Monitoring unit
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	0.5 TE
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0.02 W
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	0
NUMBER OF SWITCHES (FAULT SIGNAL)	0
RATED FAULT CURRENT	0.5 A
VOLTAGE TYPE	AC
FUNCTIONS	With auto test for earth leakage function Remote drive
DEVICE FITTING	Earth leakage switch
TYPE	<ul style="list-style-type: none"> • Accessory • Accessory for residual current circuit breaker
APPLICATION	Switchgear for industrial and advanced commercial



	applications
RATED OPERATIONAL VOLTAGE (UE) - MAX	0 V
RATED SWITCH CURRENT	0 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	0 A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

