

Eaton 24TDMEJ16

Fuse-link, medium voltage, 16 A, AC 24 kV, 2", 51 x 442 mm, back-up, DIN, with striker

PRODUCT NAME	Eaton Bussmann series medium voltage DIN fuse
CATALOG NUMBER	24TDMEJ16
UPC	051712186308
PRODUCT LENGTH/DEPTH	442 mm
PRODUCT HEIGHT	54 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	2221 g
COMPLIANCES	DIN 43625 VDE 0670-4 IEC 60282-1
CERTIFICATIONS	IEC Rated



USED WITH	270303 Fuse clip A3354710 Fuse clip
AMPERAGE RATING	16 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 442 mm
BREAKING CAPACITY	50 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
PRE ARC (I2T)	2.6 x 100
RESISTANCE	109 Ohms
WATT LOSSES	34 W
FUSE DIAMETER	51 mm
COLOR	Brown
INTERRUPT RATING	50 kAIC
CONSTRUCTION SIZE	51 x 442 mm
MOUNTING METHOD	Clip-in
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	24 kV
TYPE	Fuse
SPECIAL FEATURES	Back-up, Transformer protection, Indoor or outdoor use
APPLICATION	• transformer



	protection
	• indoor or outdoor use
FUSE TYPE	TDMEJ

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

