

Eaton 250MJ30-7

Eaton Bussmann series low voltage british standard fuse, 250A, AC 415 V, V88/J, 38 x 110 mm, gU, 82mm fixing centres, type 7

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	250MJ30-7
PRODUCT LENGTH/DEPTH	110 mm
PRODUCT HEIGHT	38 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	217.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC

AMPERAGE RATING	250 A
FITTED WITH:	Slotted tags
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Other
FUSE TYPE	MJ30
UTILIZATION CATEGORY	gU (utility/distribution protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	16 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/J
CONSTRUCTION SIZE	J
FUSE SHAPE	Dual slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	feeder pillars
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

