



□□□□

## Eaton 264699

Eaton Moeller series xPole - PLG4/6 MCB.  
PLG6, 1-pole+N, tripping characteristic: C,  
rated current In: 40 A, rated switching  
capacity IEC/EN 60898-1: 6 kA

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - PLG4/6 MCB
<b>CATALOG NUMBER</b>	264699
<b>PRODUCT LENGTH/DEPTH</b>	86 mm
<b>PRODUCT HEIGHT</b>	73 mm
<b>PRODUCT WIDTH</b>	17.5 mm
<b>PRODUCT WEIGHT</b>	0.13 kg
<b>COMPLIANCES</b>	RoHS conform



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	40 A
<b>FEATURES</b>	Additional equipment possible Concurrently switching N-neutral
<b>POLLUTION DEGREE</b>	2
<b>DEGREE OF PROTECTION</b>	IP20
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	7.4 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>TRIPPING CHARACTERISTIC</b>	C
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CURRENT LIMITING CLASS</b>	3
<b>FREQUENCY RATING - MAX</b>	60 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	1

□□

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-xeffect-faz-dc-mcb-characteristic-curve-003.jpg</a> <a href="#">eaton-xpole-plg4-6-mcb-characteristic-curve-002.jpg</a>
□□□□□	<a href="#">eaton-rccb-rcbo-g9-il019140zu.pdf</a>
□□□	<a href="#">eaton-xpole-plg4-6-mcb-wiring-diagram.jpg</a>
□□□□	<a href="#">eaton-plg6-xpole-miniature-circuit-breaker-180307-en-us.pdf</a> <a href="#">eaton-plg4-xpole-miniature-circuit-breaker-180307-en-us.pdf</a>
□□	<a href="#">eaton-xeffect-faz-dc-mcb-dimensions-005.jpg</a> <a href="#">eaton-xeffect-faz-dc-mcb-3d-drawing-003.jpg</a>

<b>VOLTAGE TYPE</b>	AC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Single-pole + N
<b>RELEASE CHARACTERISTIC</b>	C

<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Miniature circuit breaker</li> <li>• PLG6</li> </ul>
-------------	---

<b>SPECIAL FEATURES</b>	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
-------------------------	---

<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole - Switchgear for residential and commercial applications</li> </ul>
--------------------	--

<b>NUMBER OF POLES (PROTECTED)</b>	1
------------------------------------	---

<b>NUMBER OF POLES (TOTAL)</b>	2
--------------------------------	---

<b>RATED INSULATION VOLTAGE (UI)</b>	440 V
--------------------------------------	-------

<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	40 A
--	------

<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	230 V
---	-------

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V</b>	6 kA
--	------

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V</b>	6 kA
---	------

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V</b>	10 kA
--	-------

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V</b>	10 kA
--	-------

<b>RATED SWITCHING CAPACITY (IEC/EN 60898-1)</b>	6 kA
--	------

<b>STATIC HEAT</b>	0 W
--------------------	-----

