

Eaton 250NHG2BWP

Fuse-link, LV, 250 A, AC 500 V, NH2, gL/gG, IEC, dual indicator, live gripping lugs, weather resistant

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	250NHG2BWP
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	71 mm
PRODUCT WIDTH	53 mm
PRODUCT WEIGHT	651.333 g
COMPLIANCES	CE CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	250 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH2
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	23 W
CONNECTION	Blade end
CONSTRUCTION	NH2
CONSTRUCTION SIZE	NH2
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD2-D Single pole NH Fuse base Microswitch 170H0235 Microswitch 170H0236 TD2-D Triple pole NH Fuse base
MATERIAL	Ceramic body
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	Fuse
SPECIAL FEATURES	Weather resistant
APPLICATION	industrial



**RATED SWITCHING
CAPACITY AC**

120 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

