



Eaton 255898

Eaton Moeller® series P3 Main switch, P3, 63 A, surface mounting, 3 pole, STOP function, With black rotary handle and locking ring, UL/CSA

□□□□

PRODUCT NAME	Eaton Moeller® series P3 Main switch
CATALOG NUMBER	255898
PRODUCT LENGTH/DEPTH	139 mm
PRODUCT HEIGHT	240 mm
PRODUCT WIDTH	160 mm
PRODUCT WEIGHT	1.065 kg
CERTIFICATIONS	CSA File No.: 012528 UL CE CSA Class No.: 3211-05 UL 60947-4-1 VDE 0660 CSA-C22.2 No. 60947-4-1-14 CSA-C22.2 No. 94 UL Category Control No.: NLRV UL File No.: E36332 IEC/EN 60204 CSA IEC/EN 60947 IEC/EN 60947-3

PRODUCT CATEGORY	Main switch
FEATURES	Version as main switch Version as maintenance- /service switch
ACTUATOR COLOR	Black
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

DECLARATIONS OF CONFORMITY	eaton-main-switch-declaration-of-conformity-uk251292en.pdf
□□□	eaton-rotary-switches-on-off-switch-p3-main-switch-wiring-diagram.eps

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Black rotary handle and locking ring
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
RATED PERMANENT CURRENT AT AC-21, 400 V	63 A
RATED PERMANENT CURRENT AT AC-23, 400 V	63 A
RATED UNINTERRUPTED CURRENT (IU)	63 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING POWER AT 400 V	30 kW
VOLTAGE PER CONTACT PAIR IN SERIES	60 V
ACCESSORIES	Auxiliary contact or neutral conductor fitted by user.

RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	30 kW
DEVICE CONSTRUCTION	Complete device in housing
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	1.26 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
MOUNTING POSITION	As required
ACTUATOR TYPE	Door coupling rotary drive
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	3 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE	7.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	10 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	40 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	50 HP
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	4.5 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	4.5 W

NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	4 kA (Load side) 100 kA (Supply side)
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
DEGREE OF PROTECTION (FRONT SIDE)	IP65
NUMBER OF POLES	3
MOUNTING METHOD	Surface mounting
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Branch circuits, suitable as motor disconnect, (UL/CSA) Ground mounting
FUNCTIONS	Interlockable STOP function
NUMBER OF SWITCHES	1
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
SCREW SIZE	M5, Terminal screw
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
LIFESPAN, MECHANICAL	100,000 Operations
LOAD RATING	2 x I _e (with intermittent operation class 12, 25 % duty factor) 1.3 x I _e (with intermittent operation class 12, 60 % duty factor) 1.6 x I _e (with intermittent operation class 12, 40 % duty factor)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600 (UL/CSA) P600 (UL/CSA)
TERMINAL CAPACITY	2 x (1.5 - 6) mm ² , flexible

	with ferrules to DIN 46228 1 x (1.5 - 25) mm ² , flexible with ferrules to DIN 46228 2 x (2.5 - 10) mm ² , solid or stranded 14 - 2 AWG, solid or flexible with ferrule 1 x (2.5 - 35) mm ² , solid or stranded
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	60 A, Rated uninterrupted current max. (UL/CSA)
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V	2
NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V	2
RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)	640 A
RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)	600 A
RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)	590 A
RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)	340 A
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)	800 A
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	10 kA, SCCR (UL/CSA) 150A, max. Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT	80 A gG/gL, Fuse, Contacts

PROTECTION RATING	
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	51 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	55 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	44 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	22.1 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS	63 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	50 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	50 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V	50 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	63 A
RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ	18.5 kW
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	30 kW

RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ		45 kW
RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ		55 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ		30 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ		30 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ		30 kW
TIGHTENING TORQUE	26.5 lb-in, Screw terminals 3 Nm, Screw terminals	
UNINTERRUPTED CURRENT	Rated uninterrupted current I _u is specified for max. cross-section.	
RATED SWITCHING CAPACITY	10 HP at 240 V AC, single- phase 15 HP at 200 V AC, three- phase 15 HP at 240 V AC, three- phase 3 HP at 120 V AC, single- phase 40 HP at 480 V AC, three- phase 50 HP at 600 V AC, three- phase 7.5 HP at 200 V AC, single- phase	
HOUSING COLOR	Black	
HOUSING MATERIAL	Plastic	

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: