

## Eaton 259085

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 100A, N, frame1, A100

|                             |  |
|-----------------------------|--|
|                             |  |
| <b>PRODUCT NAME</b>         | Eaton Moeller series NZM molded case circuit breaker thermo-magnetic |
| <b>CATALOG NUMBER</b>       | 259085   |
| <b>PRODUCT LENGTH/DEPTH</b> | 88 mm  |
| <b>PRODUCT HEIGHT</b>       | 145 mm   |
| <b>PRODUCT WIDTH</b>        | 90 mm  |
| <b>PRODUCT WEIGHT</b>       | 1.073 kg   |
| <b>COMPLIANCES</b>          | RoHS conform   |
| <b>CERTIFICATIONS</b>       | IEC/EN 60947<br>IEC  |

|   |  |
|---|--|
| <b>AMPERAGE RATING</b>  | 100 A  |
| <b>VOLTAGE RATING</b>   | 690 V - 690 V  |
| <b>CIRCUIT BREAKER FRAME TYPE</b>   | NZM1   |
| <b>FEATURES</b>   | Protection unit  |
| <b>10.10 TEMPERATURE RISE</b>   | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>   | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>  | Meets the product standard's requirements.   |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.   |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.   |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.   |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | Meets the product standard's requirements.   |
| <b>10.2.5 LIFTING</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.2.6 MECHANICAL IMPACT</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |

|                                   |  |
|-----------------------------------|--|
| <b>CHARACTERISTIC CURVE</b>       | <a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-051.eps</a><br><br><a href="#">eaton-circuit-breaker-let-through-current-nzm-mccb-characteristic-curve-002.eps</a><br><br><a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve.eps</a>  |
| <b>DECLARATIONS OF CONFORMITY</b> | <a href="#">DA-DC-03 N1</a><br><br><a href="#">eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf</a><br><br><a href="#">eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps</a><br><br><a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-017.eps</a><br><br><a href="#">eaton-circuit-breaker-switch-nzm-mccb-3d-drawing-006.eps</a> |

|   |  |
|---|--|
| <b>10.2.7 INSCRIPTIONS</b>                                      | Meets the product standard's requirements.   |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.   |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.   |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.   |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.   |
| <b>POLLUTION DEGREE</b>   | 3  |
| <b>MOUNTING METHOD</b>  | Built-in device fixed built-in technique<br>Fixed<br>DIN rail (top hat rail)<br>mounting optional    |
| <b>CLIMATIC PROOFING</b>  | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30                       |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 21.9 W   |
| <b>UTILIZATION CATEGORY</b>                                     | A (IEC/EN 60947-2)   |
| <b>ISOLATION</b>  | 500 V AC (between auxiliary contacts and main contacts)<br>300 V AC (between the auxiliary contacts) |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 70 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C   |

|  |  |
|--|--|
| <b>AMBIENT STORAGE TEMPERATURE - MAX</b>                       | 70 °C  |
| <b>AMBIENT STORAGE TEMPERATURE - MIN</b>                       | -40 °C   |
| <b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>     | 0  |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b> | 0  |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>   | 0  |
| <b>PROTECTION AGAINST DIRECT CONTACT</b>                       | Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110                                      |
| <b>DEGREE OF PROTECTION</b>                                    | IP20<br>IP20 (basic degree of protection, in the operating controls area)                            |
| <b>DIRECTION OF INCOMING SUPPLY</b>                            | As required  |
| <b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>              | Frame clamp  |
| <b>LIFESPAN, MECHANICAL</b>                                    | 20000 operations   |
| <b>OVERVOLTAGE CATEGORY</b>                                    | III  |
| <b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>                   | IP66 (with door coupling rotary handle)<br>IP40 (with insulating surround)                           |
| <b>DEGREE OF PROTECTION (TERMINATIONS)</b>                     | IP00 (terminations, phase isolator and strip terminal)<br>IP10 (tunnel terminal)                     |
| <b>NUMBER OF POLES</b>   | Three-pole   |
| <b>TERMINAL CAPACITY (COPPER STRIP)</b>                        | Min. 2 segments of 9 mm x 0.8 mm at box terminal<br>Max. 9 segments of 9 mm x 0.8 mm at box terminal |
| <b>LIFESPAN, ELECTRICAL</b>                                    | 10000 operations at 415 V AC-1<br>10000 operations at 400 V AC-1<br>7500 operations at 690 V AC-1    |
| <b>FUNCTIONS</b>   | System and cable protection  |
| <b>TYPE</b>  | Circuit breaker  |

|  |   |
|--|---|
| <b>SPECIAL FEATURES</b>  | <ul style="list-style-type: none"> <li>• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity <math>I_{cn}</math>)</li> <li>• Rated current = rated uninterrupted current: 100 A</li> <li>• Terminal capacity hint: Up to 95 mm<sup>2</sup> can be connected depending on the cable manufacturer.</li> </ul> |
| <b>APPLICATION</b>   | Use in unearthed supply systems at 690 V  |
| <b>SHOCK RESISTANCE</b>  | 20 g (half-sinusoidal shock 20 ms)  |
| <b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>               | Front side  |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 100 A   |
| <b>POWER LOSS</b>  | 21.9 W  |
| <b>RELEASE SYSTEM</b>  | Thermomagnetic release  |
| <b>SHORT-CIRCUIT TOTAL BREAKTIME</b>                                 | < 10 ms   |
| <b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>               | 1000 A  |
| <b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>               | 600 A   |
| <b>TERMINAL CAPACITY (CONTROL CABLE)</b>                             | 0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)<br>0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)  |
| <b>TERMINAL CAPACITY (COPPER BUSBAR)</b>                             | Min. 12 mm x 5 mm direct at switch rear-side connection<br>M6 at rear-side screw connection<br>Max. 16 mm x 5 mm direct at switch rear-side   |

|  |  |
|--|--|
|  | connection   |
| <b>TERMINAL CAPACITY<br/>(COPPER SOLID<br/>CONDUCTOR/CABLE)</b>      | 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) at<br>box terminal<br>16 mm <sup>2</sup> (1x) at tunnel<br>terminal<br>10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x)<br>direct at switch rear-side<br>connection<br>6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct<br>at switch rear-side<br>connection<br>6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) at<br>box terminal          |
| <b>TERMINAL CAPACITY<br/>(ALUMINUM SOLID<br/>CONDUCTOR/CABLE)</b>    | 16 mm <sup>2</sup> (1x) at tunnel<br>terminal<br>10 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x)<br>direct at switch rear-side<br>connection<br>10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x)<br>direct at switch rear-side<br>connection  |
| <b>TERMINAL CAPACITY<br/>(COPPER STRANDED<br/>CONDUCTOR/CABLE)</b>   | 25 mm <sup>2</sup> - 95 mm <sup>2</sup> (1x) at 1-<br>hole tunnel terminal<br>6 mm <sup>2</sup> - 25 mm <sup>2</sup> (2x) at<br>box terminal<br>25 mm <sup>2</sup> (2x) direct at<br>switch rear-side<br>connection<br>10 mm <sup>2</sup> - 70 mm <sup>2</sup> (1x) at<br>box terminal<br>10 mm <sup>2</sup> - 70 mm <sup>2</sup> (1x)<br>direct at switch rear-side<br>connection |
| <b>TERMINAL CAPACITY<br/>(ALUMINUM STRANDED<br/>CONDUCTOR/CABLE)</b> | 25 mm <sup>2</sup> - 95 mm <sup>2</sup> (1x) at<br>tunnel terminal<br>25 mm <sup>2</sup> - 35 mm <sup>2</sup> (1x)<br>direct at switch rear-side<br>connection<br>25 mm <sup>2</sup> - 35 mm <sup>2</sup> (2x)<br>direct at switch rear-side<br>connection   |
| <b>HANDLE TYPE</b>   | Rocker lever   |
| <b>SHORT DELAY CURRENT<br/>SETTING (ISD) - MAX</b>                   | 0 A  |
| <b>SHORT DELAY CURRENT<br/>SETTING (ISD) - MIN</b>                   | 0 A  |
| <b>INSTANTANEOUS<br/>CURRENT SETTING (II) -<br/>MAX</b>              | 1000 A   |
| <b>INSTANTANEOUS<br/>CURRENT SETTING (II) -<br/>MIN</b>              | 600 A  |
| <b>NUMBER OF</b>   | 120  |

|  |   |
|--|---|
| <b>OPERATIONS PER HOUR - MAX</b>   |   |
| <b>OVERLOAD CURRENT SETTING (IR) - MAX</b>   | 100 A   |
| <b>OVERLOAD CURRENT SETTING (IR) - MIN</b>   | 80 A  |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>     | 85 kA   |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b> | 50 kA   |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>     | 35 kA   |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ</b>     | 10 kA   |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ</b>     | 7.5 kA  |
| <b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>                  | 105 kA  |
| <b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>                      | 74 kA   |
| <b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ</b>                      | 40 kA   |
| <b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ</b>                      | 17 kA   |
| <b>STANDARD TERMINALS</b>  | Box terminal  |
| <b>OPTIONAL TERMINALS</b>  | Connection on rear. Screw terminal. Tunnel terminal |
| <b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>                      | 187 kA  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS</b>                    | 6000 V  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE</b>   | 6000 V  |

---

**(UIMP) AT MAIN  
CONTACTS**

|                            |         |
|----------------------------|---------|
| <b>VOLTAGE RATING (DC)</b> | 450 VDC |
|----------------------------|---------|

|  |          |
|--|----------|
| <b>RATED INSULATION<br/>VOLTAGE (UI)</b> | 690 V AC |
|--|----------|

---

---

**PROJECT NAME:**

|                        |
|------------------------|
| <b>PROJECT NUMBER:</b> |
|------------------------|

---

**PREPARED BY:**

|   |
|---|
| : |
|---|

---



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

