



Eaton 265337

Eaton Moeller® series PKZM0 Motor-protective circuit-breaker, 3p, Ir=1.6-2.5A, thumb grip lockable

□□□□

PRODUCT NAME	Eaton Moeller® series PKZM0 Motor-protective circuit-breaker
CATALOG NUMBER	265337
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	93 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.294 kg
CERTIFICATIONS	VDE 0660 CSA File No.: 165628 CSA CSA-C22.2 No. 60947-4-1- 14 CE IEC/EN 60947 UL 60947-4-1 UL File No.: E36332 CSA Class No.: 3211-05 IEC/EN 60947-4-1 UL Category Control No.: NLRV UL



Powering Business Worldwide

FEATURES	Phase-failure sensitivity (according to IEC/EN 60947-4-1, VDE 0660 Part 102)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

CHARACTERISTIC CURVE	eaton-manual-motor-starters-characteristic-characteristic-curve-008.eps
DECLARATIONS OF CONFORMITY	eaton-motor-protective-circuit-breaker-declaration-of-conformity-uk251167en.pdf
□□□□□	IL03407010Z.pdf IL03402034Z
□□□	eaton-manual-motor-starters-transformer-pkzm0-wiring-diagram.eps
□□	eaton-manual-motor-starters-pkzm0-3d-drawing-008.eps eaton-manual-motor-starters-pkzm0-3d-drawing.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Padlock locking
OPERATING FREQUENCY	40 Operations/h
POLLUTION DEGREE	3
LIFESPAN, MECHANICAL	100,000 Operations (Main conducting paths)
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
ACTUATOR TYPE	Turn button
TRIPPING CHARACTERISTIC	Overload trigger: tripping class 10 A
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MAX	39 A
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	39 A
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE	80 °C

TEMPERATURE - MAX	
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	0.5 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	0.17 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	0.5 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	1 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	1.5 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	5.16 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	1.72 W
INTERNAL RESISTANCE	270 mΩ
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
ALTITUDE	Max. 2000 m
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
EXPLOSION SAFETY CATEGORY FOR DUST	PTB 10, ATEX 3013 Ex II (2) G [Ex eb Gb] [Ex db Gb] [Ex pxb Gb] Ex II (2) D [Ex tb Db] [Ex pxb Db]
CONNECTION	Screw terminals
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
MOUNTING POSITION	Can be snapped on to IEC/EN 60715 top-hat rail with 7.5 or 15 mm height.
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	Terminals: IP00 IP20
NUMBER OF POLES	Three-pole
LIFESPAN, ELECTRICAL	100,000 operations (at

	400V, AC-3)
SHOCK RESISTANCE	25 g, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms
FUNCTIONS	Phase failure sensitive Motor protection
SWITCHING CAPACITY	2.5 A (3 contacts in series), DC-5 up to 250V 2.5 A, AC-3 up to 690 V
OVERLOAD RELEASE CURRENT SETTING - MAX	2.5 A
OVERLOAD RELEASE CURRENT SETTING - MIN	1.6 A
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RATED OPERATIONAL VOLTAGE (UE) - MAX	690 V
RATED OPERATIONAL VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	2.5 A
RATED OPERATIONAL POWER AT AC-3E, 220/230 V, 50 HZ	0.37 kW
RATED OPERATIONAL POWER AT AC-3E, 380/400 V, 50 HZ	0.75 kW
RATED UNINTERRUPTED CURRENT (IU)	2.5 A
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
STRIPPING LENGTH (MAIN CABLE)	10 mm
PRODUCT CATEGORY	Motor protective circuit breaker
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
RATED OPERATIONAL POWER AT AC-3E, 440 V, 50 HZ	1.1 kW
RATED OPERATIONAL POWER AT AC-3E, 500 V, 50 HZ	1.1 kW

RATED OPERATIONAL POWER AT AC-3E, 690 V, 50 HZ	1.5 kW
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 400 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 400 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 440 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 440 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 500 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 500 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 690 V AC	5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 690 V AC	5 kA
SUITABLE FOR	Also motors with efficiency class IE3 Branch circuit: Manual type E if used with terminal, or suitable for group installations, (UL/CSA)
SHORT-CIRCUIT RELEASE	Basic device fixed 15.5 x lu ± 20% tolerance 38.8 A, I _{rm}
TERMINAL CAPACITY (SOLID)	1 x (1 - 6) mm ² 2 x (1 - 6) mm ²
RATED OPERATIONAL CURRENT (IE)	2.5 A
TEMPERATURE COMPENSATION	≤ 0.25 %/K, residual error for T > 40° -25 - 55 °C, Operating range -5 - 40 °C to IEC/EN 60947, VDE 0660
SHORT-CIRCUIT CURRENT	60 kA DC, up to 250 V DC, Main conducting paths
SHORT-CIRCUIT CURRENT RATING (GROUP PROTECTION)	50 kA, 600 V High Fault, Fuse, SCCR (UL/CSA) with 600 A, 600 V High Fault, Fuse, SCCR (UL/CSA)

	50 kA, 600 V High Fault, CB, SCCR (UL/CSA) with 600 A, 600 V High Fault, CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (TYPE E)	50 kA, 600 Y/347 V, SCCR (UL/CSA) Accessories required BK25/3-PKZ0-E 65 kA, 480 Y/277 V, SCCR (UL/CSA) 65 kA, 240 V, SCCR (UL/CSA)
SWITCH OFF TECHNIQUE	Thermomagnetic
POWER LOSS	5.16 W

□□□□:
□□□□:
□□□:
□□: