



□□□□

Eaton 259758

Eaton Moeller series NZM Shunt release,
60VAC/DC, for NZM2/3

□□□□

PRODUCT NAME	Eaton Moeller series NZM Shunt release
CATALOG NUMBER	259758
PRODUCT LENGTH/DEPTH	42 mm
PRODUCT HEIGHT	90 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.064 kg
COMPLIANCES	IEC UL/CSA RoHS conform
CERTIFICATIONS	UL (File No. E140305) CSA (File No. 22086) UL (Category Control Number DIHS) CSA (Class No. 1437-01) IEC60947 CSA certified CSA-C22.2 No. 5-09 UL489 CE marking UL listed



Powering Business Worldwide

USED WITH	NZM3(-4), N3(-4) NZM2(-4), N2(-4)
VOLTAGE RATING	0.7 - 1.1 x Us
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.

10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Screw connection
FRAME	NZM2/3
FREQUENCY RATING	50 Hz / 60 Hz / 200 Hz / 400 Hz, DC (shunt release)
MINIMUM COMMAND TIME - MAX	15 ms
MINIMUM COMMAND TIME - MIN	10 ms
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
REACTION TIME	20 ms
PICK-UP POWER CONSUMPTION (SHUNT RELEASE)	2.5 VA/W
RATED CONTROL SUPPLY VOLTAGE	60 V AC/DC
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	60 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	60 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	60 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	60 V

SUITABLE FOR	Off-load switch
CONNECTION TYPE	With bolt connection
VOLTAGE TYPE	AC
TERMINAL CAPACITY (SOLID/FLEXIBLE CONDUCTOR)	0.75 mm ² - 2.5 mm ² (2x) for undervoltage releases, off-delayed with ferrule 0.75 mm ² - 2.5 mm ² (1x) at shunt release with ferrule 18 - 14 AWG (1x) at shunt release 18 - 14 AWG (2x) for undervoltage releases, off-delayed 18 - 14 AWG (2x) at shunt release 0.75 mm ² - 2.5 mm ² (1x) for undervoltage releases, off-delayed with ferrule 0.75 mm ² - 2.5 mm ² (2x) at shunt release with ferrule 18 - 14 AWG (1x) for undervoltage releases, off-delayed

TYPE	<ul style="list-style-type: none"> • Accessory • Shunt release
-------------	--

SPECIAL FEATURES	<ul style="list-style-type: none"> • Switches are tripped by a voltage pulse or by the application of uninterrupted voltage. • If the shunt trip is live, contact with the circuit breaker's primary contacts is prevented when switched on. • Shunt releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XU... undervoltage release.
-------------------------	--

RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	60 V
--	------

RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	60 V
--	------

VOLTAGE RATING AT AC (X US) - MAX	1.1
--	-----

