

## Eaton 25H07-660

Eaton Bussmann series low voltage british standard fuse, 25A, AC 690 V, DC 460 V, V88/A2, 22 x 82 mm, gL/gG

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	25H07-660
<b>UPC</b>	051712674386
<b>PRODUCT LENGTH/DEPTH</b>	84.5 mm
<b>PRODUCT HEIGHT</b>	21 mm
<b>PRODUCT WIDTH</b>	21 mm
<b>PRODUCT WEIGHT</b>	48.75 g
<b>COMPLIANCES</b>	Contact Manufacturer

AMPERAGE RATING	25 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A2
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	71.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	460 V
CLASS	Class gG/gL
FUSE TYPE	H07-660
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.1 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/A2
CONSTRUCTION SIZE	A2
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

