



□□□□□

## Eaton 265714

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 100A, B1-M100

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
<b>CATALOG NUMBER</b>	265714
<b>PRODUCT LENGTH/DEPTH</b>	88 mm
<b>PRODUCT HEIGHT</b>	145 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	0.9 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 60947 IEC



Powering Business Worldwide

□□□□	
AMPERAGE RATING	100 A
VOLTAGE RATING	440 V - 440 V
CIRCUIT BREAKER FRAME TYPE	NZM1
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

□□	
	<a href="#">eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-032.eps</a>
CHARACTERISTIC CURVE	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-058.eps</a> <a href="#">eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-038.eps</a>
□□□□□	<a href="#">eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf</a>
□□	<a href="#">eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps</a> <a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-017.eps</a>

<b>ASSEMBLIES</b>	be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Thermal protection
<b>POLLUTION DEGREE</b>	3
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique Fixed
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	23.85 W
<b>UTILIZATION CATEGORY</b>	A (IEC/EN 60947-2)
<b>ISOLATION</b>	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to VDE 0106 part 100

<b>RATED INSULATION VOLTAGE (UI)</b>	690 V
<b>RATED OPERATING POWER AT AC-3, 230 V</b>	30 kW
<b>RATED OPERATING POWER AT AC-3, 400 V</b>	55 kW
<b>SWITCH OFF TECHNIQUE</b>	Thermomagnetic
<b>DEGREE OF PROTECTION</b>	IP20 (basic degree of protection, in the operating controls area) IP20
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Other
<b>LIFESPAN, MECHANICAL</b>	20000 operations
<b>OVERVOLTAGE CATEGORY</b>	III
<b>RATED OPERATIONAL CURRENT</b>	81 A (400 V AC-3)
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
<b>NUMBER OF POLES</b>	Three-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	Max. 9 segments of 9 mm x 0.8 mm at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal
<b>LIFESPAN, ELECTRICAL</b>	7500 operations at 415 V AC-1 7500 operations at 400 V AC-1
<b>FUNCTIONS</b>	Phase failure sensitive Motor protection
<b>TYPE</b>	Circuit breaker
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit</li> </ul>

	breaking capacity Icn) <ul style="list-style-type: none"> <li>Rated current = rated uninterrupted current: 100 A</li> <li>Terminal capacity hint: Up to 95 mm<sup>2</sup> can be connected depending on the cable manufacturer.</li> <li>With phase-failure sensitivity</li> <li>Tripping class 10 A</li> <li>IEC/EN 60947-4-1, IEC/EN 60947-2</li> <li>The circuit-breaker fulfills all requirements for AC-3 switching category.</li> </ul>
--	---

<b>APPLICATION</b>	Use in unearthed supply systems at 440 V
<b>SHOCK RESISTANCE</b>	20 g (half-sinusoidal shock 20 ms)
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	100 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	1250 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	800 A
<b>HANDLE TYPE</b>	Rocker lever
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	1250 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	800 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	120
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	100 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	80 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	30 kA

<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	25 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	18.5 kA
<b>STANDARD TERMINALS</b>	Box terminal
<b>OPTIONAL TERMINALS</b>	Connection on rear. Screw terminal. Tunnel terminal
<b>RELEASE SYSTEM</b>	Thermomagnetic release
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 10 ms
<b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>	10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) direct at switch rear-side connection 16 mm <sup>2</sup> (1x) at tunnel terminal 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 35 mm <sup>2</sup> (1x) direct at switch rear-side connection 25 mm <sup>2</sup> - 35 mm <sup>2</sup> (2x) direct at switch rear-side connection 25 mm <sup>2</sup> - 95 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x) 0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	M6 at rear-side screw connection Max. 16 mm x 5 mm direct at switch rear-side connection Min. 12 mm x 5 mm direct at switch rear-side connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) direct at switch rear-side connection 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) at box terminal 6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) at box terminal 6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> (2x) direct at switch rear-side connection

	25 mm <sup>2</sup> - 95 mm <sup>2</sup> (1x) at 1-hole tunnel terminal 10 mm <sup>2</sup> - 70 mm <sup>2</sup> (1x) at box terminal 10 mm <sup>2</sup> - 70 mm <sup>2</sup> (1x) direct at switch rear-side connection 6 mm <sup>2</sup> - 25 mm <sup>2</sup> (2x) at box terminal
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	18.5 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>	53 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>	53 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>	63 kA
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS</b>	6000 V
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	6000 V
<b>POWER LOSS</b>	23.9 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: