



□□□□

Eaton 265852

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 4p, 200A, B2-4-A200

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
CATALOG NUMBER	265852
PRODUCT LENGTH/DEPTH	149 mm
PRODUCT HEIGHT	184 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	3 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC



Powering Business Worldwide

□□□□

AMPERAGE RATING	200 A
VOLTAGE RATING	440 V - 440 V
CIRCUIT BREAKER FRAME TYPE	NZM2
FEATURES	Motor drive optional Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-050.eps
□□	eaton-circuit-breaker-nzm-mccb-dimensions-035.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
LIFESPAN, MECHANICAL	20000 operations
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
MOUNTING METHOD	Built-in device fixed built-in technique DIN rail (top hat rail) mounting optional Fixed
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	48 W
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C

NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
CURRENT RATING OF NEUTRAL CONDUCTOR	200% of phase conductor
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Max. 10 segments of 24 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched)
LIFESPAN, ELECTRICAL	10000 operations at 400 V AC-1 7500 operations at 415 V AC-1
FUNCTIONS	System and cable protection
TYPE	Circuit breaker

SPECIAL FEATURES

- Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})
- Rated current = rated uninterrupted current: 200 A
- Set value in neutral conductor is synchronous with set value I_r of main pole.

APPLICATION	Use in unearthed supply systems at 440 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	200 A
POWER LOSS	48 W
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	2000 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	1200 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 2.5 mm ² (1x) 0.75 mm ² - 1.5 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 24 mm x 8 mm direct at switch rear-side connection Min. 16 mm x 5 mm direct at switch rear-side connection M8 at rear-side screw connection
TERMINAL CAPACITY (COPPER SOLID)	10 mm ² - 16 mm ² (1x) at box terminal

CONDUCTOR/CABLE)	6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal 6 mm ² - 16 mm ² (2x) at box terminal
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	10 mm ² - 16 mm ² (2x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 70 mm ² (2x) at box terminal 25 mm ² - 185 mm ² (1x) direct at switch rear-side connection 25 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 185 mm ² (1x) at box terminal 25 mm ² - 70 mm ² (2x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 50 mm ² (2x) direct at switch rear-side connection 25 mm ² - 185 mm ² (1x) at tunnel terminal 25 mm ² - 50 mm ² (1x) direct at switch rear-side connection
HANDLE TYPE	Rocker lever
INSTANTANEOUS CURRENT SETTING (II) - MAX	10 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	6 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	200 A
OVERLOAD CURRENT SETTING (IR) - MIN	160 A
OVERLOAD CURRENT SETTING (IR)	160 A - 200 A
RATED SHORT-CIRCUIT	30 kA

BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	25 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	18.5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	53 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	53 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	63 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	690 V AC

□□□□:
□□□□:
□□□:
□□: