



□□□□

## Eaton 265967

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 4p, 630A, 400A in 4th pole, H3-4-VE630/400

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker electronic
<b>CATALOG NUMBER</b>	265967
<b>PRODUCT LENGTH/DEPTH</b>	166 mm
<b>PRODUCT HEIGHT</b>	275 mm
<b>PRODUCT WIDTH</b>	185 mm
<b>PRODUCT WEIGHT</b>	8.769 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC IEC/EN 60947



Powering Business Worldwide

<b>AMPERAGE RATING</b>	630 A
<b>VOLTAGE RATING</b>	690 V - 690 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM3
<b>FEATURES</b>	Motor drive optional Protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.

	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-028.eps</a>
	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-046.eps</a>
<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-057.eps</a>
	<a href="#">eaton-circuit-breaker-let-through-current-nzm-mccb-characteristic-curve.eps</a>
□□□□□	<a href="#">eaton-circuit-breaker-basic-device-nzmn-b-il01208009z.pdf</a>
□□	<a href="#">eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps</a>
	<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-021.eps</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique Fixed
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	178.61 W
<b>UTILIZATION CATEGORY</b>	A (IEC/EN 60947-2)
<b>ISOLATION</b>	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0

<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
<b>DEGREE OF PROTECTION</b>	IP20 (basic degree of protection, in the operating controls area) IP20
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>CURRENT RATING OF NEUTRAL CONDUCTOR</b>	200% of phase conductor 400 A
<b>LIFESPAN, MECHANICAL</b>	15000 operations
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
<b>NUMBER OF POLES</b>	Four-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	Min. 6 segments of 16 mm x 0.8 mm at box terminal Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched) Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)  10 segments of 50 mm x 1 mm (2x) at rear-side width extension Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm
<b>LIFESPAN, ELECTRICAL</b>	2000 operations at 400 V AC-3 2000 operations at 415 V

	AC-3 2000 operations at 690 V AC-3 5000 operations at 400 V AC-1 5000 operations at 415 V AC-1 3000 operations at 690 V AC-1
--	--

<b>FUNCTIONS</b>	Systems, cable, selectivity and generator protection
<b>TYPE</b>	Circuit breaker

<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity <math>I_{cn}</math>)</li> <li>• R.m.s. value measurement and "thermal memory"</li> <li>• Adjustable time delay setting to overcome current peaks <math>t_r</math> at <math>6 \times I_r</math> also infinity (without overload releases)</li> <li>• Adjustable delay time <math>t_{sd}</math></li> <li>• <math>i^2t</math> constant function: switchable</li> <li>• Rated current = rated uninterrupted current: 630 A</li> <li>• Reduced neutral conductor protection</li> <li>• Terminal capacity hint: Up to 240 mm<sup>2</sup> can be connected depending on the cable manufacturer.</li> </ul>
-------------------------	--

<b>APPLICATION</b>	Use in unearthed supply systems at 690 V
<b>SHOCK RESISTANCE</b>	20 g (half-sinusoidal shock

	20 ms)
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	630 A
<b>RELEASE SYSTEM</b>	Electronic release
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 10 ms
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>	3.3 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	3.3 kA
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX</b>	4410 A
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN</b>	472.5 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	5040 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	1260 A
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x) 0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	Max. 10 mm x 50 mm (2x) at rear-side width extension M10 at rear-side screw connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection Min. 20 mm x 5 mm direct at switch rear-side connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	300 mm <sup>2</sup> (2x) at rear-side width extension 16 mm <sup>2</sup> (1x) at tunnel terminal 16 mm <sup>2</sup> (1x) direct at switch rear-side connection 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 16 mm <sup>2</sup> (2x) at box terminal
<b>TERMINAL CAPACITY (ALUMINUM SOLID)</b>	16 mm <sup>2</sup> (1x) direct at switch rear-side

<b>CONDUCTOR/CABLE)</b>	connection 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 120 mm <sup>2</sup> (2x) at box terminal 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) direct at switch rear-side connection 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) at 2-hole tunnel terminal 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) direct at switch rear-side connection 16 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at 1-hole tunnel terminal 35 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at box terminal
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 120 mm <sup>2</sup> (1x) direct at switch rear-side connection 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) at 2-hole tunnel terminal 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at 2-hole tunnel terminal 25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal 25 mm <sup>2</sup> - 120 mm <sup>2</sup> (2x) direct at switch rear-side connection
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	4410 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	472 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	5040 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	1260 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	60
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	630 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	315 A
<b>OVERLOAD CURRENT SETTING (IR)</b>	200 A - 400 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V,</b>	150 kA

<b>50/60 HZ</b>	
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	150 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	130 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ</b>	33 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ</b>	9 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>	330 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>	286 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ</b>	143 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ</b>	74 kA
<b>STANDARD TERMINALS</b>	Screw terminal
<b>OPTIONAL TERMINALS</b>	Box terminal. Connection on rear. Tunnel terminal
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>	330 kA
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS</b>	6000 V
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	8000 V
<b>RATED INSULATION VOLTAGE (UI)</b>	1000 V AC



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

