

Eaton 266684

Eaton Moeller series NZM - Molded Case Circuit Breaker. Remote operator, 110-130VAC, for size 4

PRODUCT NAME	Eaton Moeller series NZM remote operator
CATALOG NUMBER	266684
PRODUCT LENGTH/DEPTH	189 mm
PRODUCT HEIGHT	202 mm
PRODUCT WIDTH	210 mm
PRODUCT WEIGHT	6.361 kg
COMPLIANCES	UL/CSA IEC RoHS conform
CERTIFICATIONS	IEC60947 UL489 UL (File No. E140305) UL (Category Control Number DIHS) UL listed CSA-C22.2 No. 5-09 CSA (Class No. 1437-01) CSA certified CSA (File No. 22086) CE marking

USED WITH	NZM4(-4) N(S)4(-4)
VOLTAGE RATING	110 - 130 V 50/60 Hz
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

eaton-nzm4-romete-operator-xr-il01210006z.pdf
eaton-circuit-breaker-remote-operator-nzm-remote-operator-dimensions-003.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	NZM4
BREAKING TIME	3000 ms
CLOSING DELAY	100 ms
VOLTAGE TYPE	AC
LIFESPAN, MECHANICAL	10000 operations
NUMBER OF POLES	Three-pole/Four-pole
NUMBER OF OPERATIONS PER HOUR - MAX	20
VOLTAGE TOLERANCE - MAX	1.1
VOLTAGE TOLERANCE - MIN	.85
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	130 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	130 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60	110 V

HZ - MIN	
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED OPERATING FREQUENCY	50 Hz
SIGNAL DURATION OF REMOTE OPERATOR AT SWITCH OFF - MIN	500 ms
SIGNAL DURATION OF REMOTE OPERATOR AT SWITCH ON - MIN	30 ms
SWITCH DRIVE TYPE	Motor drive
TERMINAL CAPACITY (SOLID/FLEXIBLE CONDUCTOR)	0.75 mm ² - 2.5 mm ² with ferrule 18 - 14 AWG
TYPE	<ul style="list-style-type: none"> • Accessory • Remote operator, can be synchronized
SPECIAL FEATURES	<ul style="list-style-type: none"> • Cannot be combined with switch-disconnector PN... • Do not install M22-CK11(20/02) dual auxiliary contacts in the right-hand side auxiliary contact slot in NZM4-XR
OPERATING VOLTAGE - MAX	1.1 x Us
OPERATING VOLTAGE - MIN	0.85 x Us
POWER CONSUMPTION	350 VA (110 - 130 V AC)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

