

## Eaton 266685

Eaton Moeller series NZM - Molded Case Circuit Breaker. Remote operator, 208-240VAC, for size 4

<b>PRODUCT NAME</b>	Eaton Moeller series NZM remote operator
<b>CATALOG NUMBER</b>	266685
<b>PRODUCT LENGTH/DEPTH</b>	189 mm
<b>PRODUCT HEIGHT</b>	202 mm
<b>PRODUCT WIDTH</b>	210 mm
<b>PRODUCT WEIGHT</b>	6.1 kg
<b>COMPLIANCES</b>	IEC UL/CSA RoHS conform
<b>CERTIFICATIONS</b>	CSA certified CSA (Class No. 1437-01) UL listed UL489 UL (File No. E140305) UL (Category Control Number DIHS) CE marking IEC60947 CSA (File No. 22086) CSA-C22.2 No. 5-09

<b>USED WITH</b>	N(S)4(-4) NZM4(-4)
<b>VOLTAGE RATING</b>	208 - 240 V 50/60 Hz
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.

<a href="#">eaton-nzm4-romete-operator-xr-il01210006z.pdf</a>	
<a href="#">eaton-circuit-breaker-remote-operator-nzm-remote-operator-dimensions-003.eps</a>	

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FRAME</b>	NZM4
<b>BREAKING TIME</b>	3000 ms
<b>CLOSING DELAY</b>	100 ms
<b>VOLTAGE TYPE</b>	AC
<b>LIFESPAN, MECHANICAL</b>	10000 operations
<b>NUMBER OF POLES</b>	Three-pole/Four-pole
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	20
<b>VOLTAGE TOLERANCE - MAX</b>	1.1
<b>VOLTAGE TOLERANCE - MIN</b>	.85
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX</b>	240 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b>	208 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX</b>	240 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60</b>	208 V

<b>HZ - MIN</b>	
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	0 V
<b>RATED OPERATING FREQUENCY</b>	50 Hz
<b>SIGNAL DURATION OF REMOTE OPERATOR AT SWITCH OFF - MIN</b>	500 ms
<b>SIGNAL DURATION OF REMOTE OPERATOR AT SWITCH ON - MIN</b>	30 ms
<b>SWITCH DRIVE TYPE</b>	Motor drive
<b>TERMINAL CAPACITY (SOLID/FLEXIBLE CONDUCTOR)</b>	0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> with ferrule 18 - 14 AWG
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Accessory</li> <li>• Remote operator, can be synchronized</li> </ul>
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• Cannot be combined with switch-disconnector PN...</li> <li>• Do not install M22-CK11(20/02) dual auxiliary contacts in the right-hand side auxiliary contact slot in NZM4-XR</li> </ul>
<b>OPERATING VOLTAGE - MAX</b>	1.1 x Us
<b>OPERATING VOLTAGE - MIN</b>	0.85 x Us
<b>POWER CONSUMPTION</b>	350 VA (110 - 130 V AC)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

