



□□□□□

Eaton 271129

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 225A, N, frame 2, VEF225-NA

□□□□

PRODUCT NAME	Eaton Moeller series NZM - Molded case circuit breaker
CATALOG NUMBER	271129
PRODUCT LENGTH/DEPTH	149 mm
PRODUCT HEIGHT	195 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	2.345 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	CSA-C22.2 No. 5-09 UL/CSA IEC 60947-2 UL (File No. E31593) UL 489 IEC/EN 60947 CSA (File No. 22086) IEC CE marking Specially designed for North America UL listed CSA (Class No. 1432-01) UL (Category Control Number DIVQ) CSA certified

AMPERAGE RATING	225 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM2
FEATURES	Protection unit Motor drive optional
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

	eaton-circuit-breaker-nzm-mccb-characteristic-curve-054.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-043.eps eaton-circuit-breaker-current-nzm-mccb-characteristic-curve-006.eps
□□	eaton-circuit-breaker-nzm-mccb-dimensions-019.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Fixed Built-in device fixed built-in technique
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	41.77 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
LOW-VOLTAGE HBC FUSE	355 A gG/gL

- MAX	
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 (basic degree of protection, in the operating controls area) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	300 A (380/400 V AC-1, making and breaking capacity) 300 A (415 V AC-1, making and breaking capacity) 225 A (690 V AC -1, making and breaking capacity) 225 A (660-690 V AC-3, making and breaking capacity)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Max. 10 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 9 mm x 0.8 mm at box terminal

LIFESPAN, ELECTRICAL	5000 operations at 690 V AC-3 7500 operations at 690 V AC-1 10000 operations at 400 V AC-1 6500 operations at 415 V AC-3 6500 operations at 400 V AC-3
FUNCTIONS	Systems, cable, selectivity and generator protection Current limiting circuit breaker
TYPE	Circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 225 A • Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate. • Fixed overload releases I_r • R.m.s. value measurement and "thermal memory" • adjustable time delay setting to overcome current peaks t_r: 2 – 20 s at $6 \times I_r$ • Adjustable delay time t_{sd}: Steps: 0, 20, 60, 100, 200, 300, 500, 750, 1000 ms • i^2t constant function: fixed OFF

APPLICATION	<ul style="list-style-type: none"> • Branch circuits, feeder circuits • Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	225 A
POWER LOSS	41.77 W
RELEASE SYSTEM	Electronic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	1.9 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	1.9 kA
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	2250 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	450 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	2700 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	2700 A
TERMINAL CAPACITY (CONTROL CABLE)	14 mm ² - 18 mm ² (1x) 16 mm ² - 18 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	Min. 16 mm x 5 mm direct at switch rear-side connection M8 at rear-side screw connection Max. 20 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	6 mm ² - 12 mm ² (1x) at box terminal 6 mm ² - 11 mm ² (1x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (ALUMINUM SOLID)	16 mm ² (1x) at tunnel terminal

CONDUCTOR/CABLE)	
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	4 mm ² - 350 mm ² (1x) at box terminal 4 mm ² - 350 mm ² (1x) at tunnel terminal 4 mm ² - 3/0 mm ² (1x) direct at switch rear-side connection
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	2250 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	450 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	2700 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	2700 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	225 A
OVERLOAD CURRENT SETTING (IR) - MIN	225 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	85 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	35 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	25 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	74 kA
RATED SHORT-CIRCUIT	53 kA

MAKING CAPACITY ICM AT 525 V, 50/60 HZ	
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
STANDARD TERMINALS	Screw terminal
RATED OPERATING VOLTAGE UE (UL) - MAX	600Y/347 V, 480 V
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	187 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	1000 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

