

## Eaton 265807

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 4p, 100A, B, frame 1, 4-A100

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
<b>CATALOG NUMBER</b>	265807
<b>PRODUCT LENGTH/DEPTH</b>	84.5 mm
<b>PRODUCT HEIGHT</b>	145 mm
<b>PRODUCT WIDTH</b>	120 mm
<b>PRODUCT WEIGHT</b>	1.336 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC IEC/EN 60947

<b>AMPERAGE RATING</b>	100 A
<b>VOLTAGE RATING</b>	440 V - 440 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM1
<b>FEATURES</b>	Protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.

## CHARACTERISTIC CURVE

[eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-038.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-051.eps](#)

[eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-032.eps](#)

[eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-018.eps](#)

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>MOUNTING METHOD</b>	Built-in device fixed built-in technique Fixed DIN rail (top hat rail) mounting optional
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	21.9 W
<b>UTILIZATION CATEGORY</b>	A (IEC/EN 60947-2)
<b>ISOLATION</b>	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C

<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
<b>DEGREE OF PROTECTION</b>	IP20 IP20 (basic degree of protection, in the operating controls area)
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Frame clamp
<b>CURRENT RATING OF NEUTRAL CONDUCTOR</b>	200% of phase conductor
<b>LIFESPAN, MECHANICAL</b>	20000 operations
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
<b>NUMBER OF POLES</b>	Four-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	Max. 9 segments of 9 mm x 0.8 mm at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal
<b>LIFESPAN, ELECTRICAL</b>	7500 operations at 400 V AC-1 7500 operations at 415 V AC-1
<b>FUNCTIONS</b>	System and cable protection
<b>TYPE</b>	Circuit breaker

## SPECIAL FEATURES

- Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity  $I_{cn}$ )
- Rated current = rated uninterrupted current: 100 A
- Set value in neutral conductor is synchronous with set value  $I_r$  of main pole.
- Terminal capacity hint: Up to 95 mm<sup>2</sup> can be connected depending on the cable manufacturer.

APPLICATION	Use in unearthed supply systems at 440 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	100 A
POWER LOSS	21.9 W
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	1000 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	600 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x) 0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 16 mm x 5 mm direct at switch rear-side

	connection M6 at rear-side screw connection Min. 12 mm x 5 mm direct at switch rear-side connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) at box terminal 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) direct at switch rear-side connection 16 mm <sup>2</sup> (1x) at tunnel terminal 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) at box terminal 6 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> (1x) at tunnel terminal 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 10 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) direct at switch rear-side connection
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	6 mm <sup>2</sup> - 25 mm <sup>2</sup> (2x) at box terminal 10 mm <sup>2</sup> - 70 mm <sup>2</sup> (1x) at box terminal 25 mm <sup>2</sup> (2x) direct at switch rear-side connection 10 mm <sup>2</sup> - 70 mm <sup>2</sup> (1x) direct at switch rear-side connection 25 mm <sup>2</sup> - 95 mm <sup>2</sup> (1x) at 1- hole tunnel terminal
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 35 mm <sup>2</sup> (1x) direct at switch rear-side connection 25 mm <sup>2</sup> - 35 mm <sup>2</sup> (2x) direct at switch rear-side connection 25 mm <sup>2</sup> - 95 mm <sup>2</sup> (1x) at tunnel terminal
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	0 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	0 A
<b>INSTANTANEOUS CURRENT SETTING (II) -</b>	10 A

<b>MAX</b>	
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	6 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	120
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	100 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	80 A
<b>OVERLOAD CURRENT SETTING (IR)</b>	80 A - 100 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	30 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	25 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	18.5 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ</b>	53 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ</b>	53 kA
<b>STANDARD TERMINALS</b>	Box terminal
<b>OPTIONAL TERMINALS</b>	Connection on rear. Screw terminal. Tunnel terminal
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ</b>	63 kA
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS</b>	6000 V
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	6000 V
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

