



□□□□□

Eaton 266106

Eaton Moeller® series LS Position switch,
Actuating rod, Complete unit, 1 N/O, 1 NC,
Snap-action contact - Yes, Cage Clamp,
Yellow, Insulated material, -25 - +70 °C

□□□□

PRODUCT NAME	Eaton Moeller® series LS Position switch
CATALOG NUMBER	266106
PRODUCT LENGTH/DEPTH	33.5 mm
PRODUCT HEIGHT	140 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	0.078 kg
CERTIFICATIONS	UL 508 UL Category Control No.: NKCR UL CSA File No.: 012528 CSA-C22.2 No. 14 IEC/EN 60947-5 CSA IEC/EN 60947 UL File No.: E29184 CE CSA Class No.: 3211-03
CATALOG NOTES	The operating head can be rotated 90° to enable adaptation to the specified approach direction

□□□□

TYPE	Safety position switch
FEATURES	Snap-action contact Forced opening Positive opening
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

□□

DECLARATIONS OF CONFORMITY	eaton-position-switch-declaration-of-conformity-uk251032en.pdf
□□□□□	IL053001ZU
□□□	eaton-position-switches-contact-ls-wiring-diagram.eps
□□□□□	eaton-position-switches-diagram-ls-contact-travel-diagram-018.eps
□□	eaton-position-switches-actuation-ls-dimensions.eps eaton-position-switches-actuation-ls-dimensions-002.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Cable entry metrical
ENCLOSURE MATERIAL FINISHING	Other
OPERATING FREQUENCY	6000 Operations/h
POLLUTION DEGREE	3
ACTUATOR ALIGNMENT	Roller cam crossed
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
ENCLOSURE MATERIAL	Insulated material Plastic
ENCLOSURE TYPE	Cuboid
RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.6 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 125 V	0.8 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.3 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	3 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	6 A

SENSOR HEIGHT	61 mm
SENSOR LENGTH	33.5 mm
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
WIDTH SENSOR	31 mm
PRODUCT CATEGORY	Actuating rod
ACTION	2021118113756-Mechanical Limit Switches.xlsm-Data
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Yellow Cover
ACTUATING FORCE AT BEGINNING/END OF STROKE	1.0 N/8.0 N
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
ACTUATOR TYPE	Actuating rod
ACTUATING TORQUE OF ROTARY DRIVES	0.2 Nm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
DIAMETER SENSOR	0 mm
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.17 W
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF SAFETY AUXILIARY CONTACTS	1
RATED INSULATION	400 V

VOLTAGE (UI)	
RATED OPERATIONAL CURRENT (IE) AT AC-15, 125 V	6 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	6 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V	6 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	4 A
MOUNTING POSITION	As required
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 10,000,000 switching operations (Statistically determined, at 24 V DC/5 mA) 1 failure per 5,000,000 switching operations (statistically determined, at 5 V DC/1 mA)
CONNECTION TYPE	Cage Clamp
DEGREE OF PROTECTION	IP66/IP67 NEMA Other
INTERFACE TYPE	None
SWITCH FUNCTION TYPE	Quick-break switch
LIFESPAN	8,000,000 mechanical Operations
REPETITION ACCURACY	0.15 mm (Contacts/switching capacity)
SHOCK RESISTANCE	25 g, Standard-action contact, Mechanical, Half-sinusoidal shock 20 ms
SUPPLY FREQUENCY	Max. 400 Hz, Contacts
SUITABLE FOR	Safety functions
OPERATING SPEED	L = 130 mm Max. 1.5 m/s (with DIN cam, mechanical actuation)
SHORT-CIRCUIT PROTECTION RATING	Max. 6 A gG/gL, Fuse, Contacts
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.5 - 1.5) mm ²

TERMINAL CAPACITY (SOLID)	1 x (0.5 - 2.5) mm ²
------------------------------	---------------------------------
