



Eaton 266815

Eaton Moeller series NZM - Molded Case Circuit Breaker. Module plate 1-hole 4p, size 4

□□□□

PRODUCT NAME	Eaton Moeller series NZM connection type
CATALOG NUMBER	266815
PRODUCT LENGTH/DEPTH	61 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	180 mm
PRODUCT WEIGHT	0.825 kg
COMPLIANCES	IEC RoHS conform

USED WITH	NZM4-4, N4-4
AMPERAGE RATING	□ 1250 A
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND	Meets the product

□□□□□	eaton-circuit-breakers-nzm4-xkm1-2-2s-module-plate-1-2-hole-instruction-leaflet-il01210011z.pdf
□□	eaton-circuit-breaker-plate-nzm-module-plate-dimensions-002.eps eaton-circuit-breaker-plate-nzm-module-plate-3d-drawing-002.eps eaton-circuit-breaker-plate-nzm-module-plate-3d-drawing-003.eps

CREEPAGE DISTANCES	standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	NZM4
SUITABLE FOR	Copper cable lugs Four-pole
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	10 segments of 40 mm x 1 mm (2x) 10 segments of 50 mm x 1 mm (2x)
TERMINAL CAPACITY (FLEXIBLE CABLE)	120 mm ² - 300 mm ² (1x) Max. 600 AWG/kcmil (2x) 250 - 600 AWG/kcmil (1x) 95 mm ² - 300 mm ² (2x)
TYPE	Accessory Module plate Terminal
SPECIAL FEATURES	One hole
TERMINAL CAPACITY (COPPER BUSBAR)	40 mm x 10 mm (2x) 50 mm x 10 mm (2x)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

