

Eaton 276400

Eaton Moeller® series DILA Contactor relay,
380 V 50 Hz, 440 V 60 Hz, 2 N/O, 2 NC, Screw
terminals, AC operation

PRODUCT NAME	Eaton Moeller® series DILA Control relay
CATALOG NUMBER	276400
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	68 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.237 kg
CERTIFICATIONS	EN 60947-5-1 VDE 0660 CSA IEC/EN 60947-4-1 UL CSA-C22.2 No. 14-05 UL Category Control No.: NKCR IEC/EN 60947 UL 508 UL File No.: E29184 CE CSA Class No.: 3211-03 CSA File No.: 012528

FEATURES	Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

eaton-contactors-dila-dilm7-15-dilmp20-il03407013z.pdf
eaton-contactors-module-dilm-dimensions.eps eaton-contactors-frame-dilm-dimensions.eps eaton-contactors-dilm-3d-drawing-007.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Positive operation contacts
OPERATING FREQUENCY	9000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W

HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.5 W
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS, DELAYED SWITCHING)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS, LEADING)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	2
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	380 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	380 V
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
CONNECTION	Screw terminals
APPLICATION	Contactor relays
PRODUCT CATEGORY	DILA relays
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	16 A

VOLTAGE TYPE OF OPERATING VOLTAGE	AC/DC
RATED SWITCH CURRENT	16 A
OPERATING VOLTAGE AT AC, 50 HZ - MIN	17 V
OPERATING VOLTAGE AT AC, 50 HZ - MAX	500 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	17 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	500 V
OPERATING VOLTAGE AT DC - MIN	24 VDC
OPERATING VOLTAGE AT DC - MAX	220 VDC
SCREWDRIVER SIZE	0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
VOLTAGE TYPE	AC
CODE NUMBER	22D
DEGREE OF PROTECTION	IP20
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	$\lambda < 5 \times 10^{-7}$ (1 failure at 2,000,000 operations for $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)
CONNECTION TYPE (AUXILIARY CIRCUIT)	Screw connection
DUTY FACTOR	100 %
LIFESPAN, MECHANICAL	20,000,000 Operations (AC operated)
MOUNTING METHOD	DIN-rail/screw
PICK-UP VOLTAGE	0.8 - 1.1 V AC x U_c (voltage tolerance - single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz)
POWER CONSUMPTION, PICK-UP, 50 HZ	24 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
SAFE ISOLATION	400 V AC, Between auxiliary contacts, According to EN 61140 400 V AC, Between coil and auxiliary contacts,

	According to EN 61140
POWER CONSUMPTION, PICK-UP, 60 HZ	24 VA, AC, Single- frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
SCREW SIZE	M3.5, Terminal screw
POWER CONSUMPTION, SEALING, 60 HZ	1.4 W, AC, Single- frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
RATED OPERATIONAL CURRENT (IE)	1 A at 220 V, DC L/R \leq 50 ms (with 3 contacts in series) 1 A at 220 V, DC L/R \leq 15 ms (with 1 contact in series) 4 A at 60 V, DC L/R \leq 50 ms (with 3 contacts in series) 2 A at 110 V, DC L/R \leq 50 ms (with 3 contacts in series) 6 A at 60 V, DC L/R \leq 15 ms (with 1 contact in series) 10 A at 60 V, DC L/R \leq 15 ms (with 2 contacts in series) 4 A at 24 V, DC L/R \leq 50 ms (with 3 contacts in series) 6 A at 110 V, DC L/R \leq 15 ms (with 3 contacts in series) 10 A at 24 V, DC L/R \leq 15 ms (with 1 contact in series) 3 A at 110 V, DC L/R \leq 15 ms (with 1 contact in series) 5 A at 220 V, DC L/R \leq 15 ms (with 3 contacts in series) 16 A
POWER CONSUMPTION, SEALING, 50 HZ	3.4 VA, AC, Single- frequency coil 50 Hz and Dual-frequency coil 50/60 Hz 1.4 W, AC, Single- frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	15 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS,	A600, AC operated (UL/CSA)

PILOT DUTY)	P300, DC operated (UL/CSA)
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	440 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	440 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 500 V	1.5 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	15.5 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	1.4 W
STRIPPING LENGTH (MAIN CABLE)	10 mm
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	21 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN	15 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	18 ms
SWITCHING TIME (AC	9 ms

**OPERATED, MAKE
CONTACTS, OPENING
DELAY) - MIN**

**TERMINAL CAPACITY
(FLEXIBLE WITH
FERRULE)**

2 x (0.75 - 2.5) mm², Screw
terminals
1 x (0.75 - 2.5) mm², Screw
terminals

SHOCK RESISTANCE

5 g, N/C auxiliary contact,
Basic unit with auxiliary
contact module,
Mechanical, according to
IEC/EN 60068-2-27, Half-
sinusoidal shock 10 ms
7 g, N/O auxiliary contact,
Basic unit with auxiliary
contact module,
Mechanical, according to
IEC/EN 60068-2-27, Half-
sinusoidal shock 10 ms

**TERMINAL CAPACITY
(SOLID/STRANDED AWG)**

18 - 14, Screw terminals

**SHORT-CIRCUIT
PROTECTION RATING
WITHOUT WELDING**

10 A gG/gL, 500 V, Max.
Fuse, Contacts

**TERMINAL CAPACITY
(SOLID)**

1 x (0.75 - 4) mm², Screw
terminals
2 x (0.75 - 2.5) mm², Screw
terminals

ACTUATING VOLTAGE

380 V 50 Hz, 440 V 60 Hz

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

