



Eaton 266971

Eaton Distribution parts. Residual-current circuit breaker trip block for PLS. 40A, 4 p, 30mA, type G

□□□□

PRODUCT NAME	Eaton Moeller series xPole - PBSM RCCB add-on unit
CATALOG NUMBER	266971
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	130 mm
PRODUCT WEIGHT	0.31 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 61009

AMPERAGE RATING

40 A

FEATURES

Add-on residual current protection unit
Additional equipment possible

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF

Does not apply, since the

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Interlocking device
FRAME	45 mm
FREQUENCY RATING	50 Hz
POLLUTION DEGREE	2
LIFESPAN, MECHANICAL	20000 operations
MOUNTING METHOD	Fix mounted onto PLS DIN rail
CLIMATIC PROOFING	25-55 °C / 90-95% relative humidity according to IEC 60068-2
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	22 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	10 kA 0 kA
BUILT-IN WIDTH (NUMBER OF UNITS)	125 mm (4 SU)
BUSBAR MATERIAL THICKNESS	0.8 mm - 2 mm
TERMINAL PROTECTION	Finger and hand touch safe, DGUV VS3, EN 50274
TERMINALS (TOP AND BOTTOM)	Lift terminals

AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	76 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	35 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	0.75 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	35 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	0.75 mm ²
FAULT CURRENT RATING	30 mA
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MAX	60 °C
PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MIN	-35 °C
DEGREE OF PROTECTION	IP20 IP20, IP40 with suitable enclosure
IMPULSE WITHSTAND CURRENT	Surge-proof, 3 kA
NUMBER OF POLES	Four-pole
LEAKAGE CURRENT TYPE	AC
LIFESPAN, ELECTRICAL	4000 operations
TYPE	Ambient temperature hint: Starting at 40 °C, the max. permissible continuous current decreases by 3% for every 1 °C
SPECIAL FEATURES	• Add-on residual current protection unit • PBSM • Type G (ÖVE E

8601)

APPLICATION

- Switchgear for residential and commercial applications
- xPole - Switchgear for residential and commercial applications

FUNCTIONS

Short-time delayed tripping

SENSITIVITY TYPE

AC current sensitive

RATED FAULT CURRENT - MAX

0.03 A

RATED FAULT CURRENT - MIN

0.03 A

RATED INSULATION VOLTAGE (UI)

440 V

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)

40 A

RATED OPERATIONAL VOLTAGE (UE) - MAX

400 V

STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT

0 W

SURGE CURRENT CAPACITY

0.25 kA

VOLTAGE RATING - MAX

415 V

VOLTAGE RATING - MIN

240 V

WIDTH IN NUMBER OF MODULAR SPACINGS

7

TRIPPING TIME

Short time-delayed
10 ms delayed (Type G)

RATED SHORT-CIRCUIT STRENGTH

Same as connected PLS up to max. 10 kA

