

Eaton 276426

Eaton Moeller® series DILA Auxiliary contact module, 4 pole, Ith= 16 A, 2 N/O, 2 NC, Front fixing, Screw terminals, DILA, DILM7 - DILM38

PRODUCT NAME	Eaton Moeller® series DILA Accessory Auxiliary contact module
CATALOG NUMBER	276426
UPC	782116354597
PRODUCT LENGTH/DEPTH	45 mm
PRODUCT HEIGHT	38 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.049 kg
CERTIFICATIONS	IEC/EN 60947-4-1 CSA-C22.2 No. 14-05 UL Category Control No.: NKCR CSA UL 508 VDE 0660 CSA Class No.: 3211-03 CE IEC/EN 60947 CSA File No.: 012528 UL UL File No.: E29184

TYPE	Front mounting auxiliary contact
FEATURES	Interlocked opposing contacts within an auxiliary contact module (according to IEC 60947-5-1 Annex L)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to

DECLARATIONS OF CONFORMITY	eaton-accessory-declaration-of-conformity-uk251276en.pdf
MCAD MODEL	dil_a_xhi_4.stp
	eaton-contactors-dila-dilm7-15-dilmp20-il03407013z.pdf
	eaton-contactors-module-dilm-dimensions.eps
	eaton-contactors-frame-dilm-dimensions.eps
	eaton-contactors-contact-dilm-accessory-3d-drawing-008.eps

	be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Screw connection
FITTED WITH:	Interlocked opposing contacts Switching elements according to EN 50005
OPERATING FREQUENCY	9000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C

AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	16 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.16 W
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF SWITCHES (FAULT SIGNAL)	0
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
SCREWDRIVER SIZE	0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
MOUNTING METHOD	Front fastening
CONNECTION	Screw terminals
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	$\lambda < 5 \times 10^{-7}$ (1 failure at 2,000,000 operations for $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA) $\lambda < 5 \times 1/10^7$ (1 failure at 2,000,000 operations for $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)
DEGREE OF PROTECTION	IP20
CODE NUMBER	62E in combination with DILA(C)-40 44 in combination with

	DILA(C)-22 53 in combination with DILA(C)-31
MODEL	Top mounting
LAMP HOLDER	None
FUNCTIONS	For standard applications
SAFE ISOLATION	400 V AC, Between auxiliary contacts, According to EN 61140 400 V AC, Between coil and auxiliary contacts, According to EN 61140
RATED OPERATIONAL CURRENT (IE)	10 A at 60 V, DC L/R $\leq$ 15 ms (with 2 contacts in series) 6 A at 60 V, DC L/R $\leq$ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R $\leq$ 15 ms (with 1 contact in series) 0.5 A at 110 V, DC L/R $\leq$ 50 ms (with 3 contacts in series) 1 A at 60 V, DC L/R $\leq$ 50 ms (with 3 contacts in series) 5 A at 220 V, DC L/R $\leq$ 15 ms (with 3 contacts in series) 2.5 A at 24 V, DC L/R $\leq$ 50 ms (with 3 contacts in series) 10 A at 24 V, DC L/R $\leq$ 15 ms (with 1 contact in series) 0.25 A at 220 V, DC L/R $\leq$ 50 ms (with 3 contacts in series) 3 A at 110 V, DC L/R $\leq$ 15 ms (with 1 contact in series) 6 A at 110 V, DC L/R $\leq$ 15 ms (with 3 contacts in series)
SCREW SIZE	M3.5, Terminal screw
LIFESPAN, ELECTRICAL	1,300,000 Operations (at 230 V, AC-15, 3 A)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	1 A, 250 V DC, (UL/CSA) 10 A, 600 V AC, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	P300, DC operated (UL/CSA) A600, AC operated (UL/CSA)

LIFESPAN, MECHANICAL	10,000,000 Operations (DC operated) 10,000,000 Operations (AC operated)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
NUMBER OF POLES	Four-pole
SHORT-CIRCUIT PROTECTION RATING WITHOUT WELDING	10 A gG/gL, 500 V, Max. Fuse, Contacts
SHORT-CIRCUIT PROTECTION RATING	Max. 10 A gG/gL, Fuse, Without welding, Auxiliary contacts
RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 500 V	1.5 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.5 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.25 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	2.5 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 60 V	1 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	4 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	500 V
TERMINAL CAPACITY	1 x (0.75 - 2.5) mm ² , Screw

(FLEXIBLE WITH FERRULE)	terminals 2 x (0.75 - 2.5) mm ² , Screw terminals
TERMINAL CAPACITY (SOLID)	2 x (0.75 - 2.5) mm ² , Screw terminals 1 x (0.75 - 2.5) mm ² , Screw terminals
TIGHTENING TORQUE	1.2 Nm, Screw terminals
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14, Screw terminals
SHOCK RESISTANCE	5 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

