



□□□□□

Eaton 276441

Eaton Moeller® series DILA Contactor relay,
230 V 50 Hz, 240 V 60 Hz, 4 N/O, Spring-
loaded terminals, AC operation

□□□□

PRODUCT NAME	Eaton Moeller® series DILA Control relay
CATALOG NUMBER	276441
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	68 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.225 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	UL 508 IEC 60947-4-1 CSA Std. C22.2 No. 14-05 EN 60947-4-1 VDE EN 60947-5-1 CSA File No.: 012528 UL UL Category Control No.: NKCR UL File No.: E29184 IEC/EN 60947-4-1 CSA CSA Class No.: 3211-03 VDE 0660 CE IEC/EN 60947 CSA-C22.2 No. 14-05
CATALOG NOTES	This item can only be ordered until December 31, 2023 with a maximum delivery date of May 31, 2024.

FEATURES	Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

DECLARATIONS OF CONFORMITY	eaton-control-relay-declaration-of-conformity-uk251205en.pdf
00000	eaton-contactors-dila-dilm7-15-dilmp20-il03407013z.pdf
000	eaton-contactors-contact-diler-relay-wiring-diagram.eps
00	eaton-contactors-contact-dilm-dimensions.eps eaton-contactors-frame-dilm-dimensions.eps eaton-contactors-dilm-3d-drawing-008.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Positive operation contacts
OPERATING FREQUENCY	9000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-	0.5 W

DEPENDENT PVID	
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS, DELAYED SWITCHING)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	4
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS, LEADING)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	4
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	230 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	230 V
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
CONNECTION	Spring-loaded terminals
APPLICATION	Contactor relays
PRODUCT CATEGORY	DILA relays
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	16 A
VOLTAGE TYPE OF OPERATING VOLTAGE	AC/DC
RATED SWITCH CURRENT	16 A
OPERATING VOLTAGE AT AC, 50 HZ - MIN	17 V

OPERATING VOLTAGE AT AC, 50 HZ - MAX	500 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	17 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	500 V
OPERATING VOLTAGE AT DC - MIN	24 VDC
OPERATING VOLTAGE AT DC - MAX	220 VDC
SCREWDRIVER SIZE	0.6 x 3.5 mm, Spring-loaded terminals
VOLTAGE TYPE	AC
CODE NUMBER	40E
DEGREE OF PROTECTION	IP20
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	$\lambda < 5 \times 10^{-7}$ (1 failure at 2,000,000 operations for $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)
CONNECTION TYPE (AUXILIARY CIRCUIT)	Spring clamp connection
DUTY FACTOR	100 %
LIFESPAN, MECHANICAL	20,000,000 Operations (AC operated)
MOUNTING METHOD	DIN-rail/screw
PICK-UP VOLTAGE	0.8 - 1.1 V AC x U_c (voltage tolerance - single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz)
POWER CONSUMPTION, PICK-UP, 50 HZ	24 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
SAFE ISOLATION	400 V AC, Between auxiliary contacts, According to EN 61140 400 V AC, Between coil and auxiliary contacts, According to EN 61140
POWER CONSUMPTION, PICK-UP, 60 HZ	24 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
POWER CONSUMPTION, SEALING, 60 HZ	1.4 W, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
RATED OPERATIONAL CURRENT (IE)	10 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in

	series) 3 A at 110 V, DC L/R ≤ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R ≤ 15 ms (with 1 contact in series) 4 A at 24 V, DC L/R ≤ 50 ms (with 3 contacts in series) 6 A at 110 V, DC L/R ≤ 15 ms (with 3 contacts in series) 4 A at 60 V, DC L/R ≤ 50 ms (with 3 contacts in series) 5 A at 220 V, DC L/R ≤ 15 ms (with 3 contacts in series) 2 A at 110 V, DC L/R ≤ 50 ms (with 3 contacts in series) 10 A at 60 V, DC L/R ≤ 15 ms (with 2 contacts in series) 6 A at 60 V, DC L/R ≤ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R ≤ 50 ms (with 3 contacts in series) 16 A
POWER CONSUMPTION, SEALING, 50 HZ	3.4 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz 1.4 W, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	15 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED INSULATION	690 V

VOLTAGE (UI)	
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 500 V	1.5 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	15.5 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	1.4 W
STRIPPING LENGTH (MAIN CABLE)	10 mm
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	21 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN	15 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	18 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN	9 ms
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	2 x (0.75 - 1.5) mm ² , Spring-loaded terminals with or without ferrule DIN 46228 1 x (0.75 - 1.5) mm ² , Spring-loaded terminals with or without ferrule DIN 46228
SHOCK RESISTANCE	5 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Basic unit with auxiliary

	contact module, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14, Spring-loaded terminals
SHORT-CIRCUIT PROTECTION RATING WITHOUT WELDING	10 A gG/gL, 500 V, Max. Fuse, Contacts
TERMINAL CAPACITY (SOLID)	2 x (0.75 - 2.5) mm², Spring-loaded terminals 1 x (0.75 - 2.5) mm², Spring-loaded terminals
ACTUATING VOLTAGE	230 V 50 Hz, 240 V 60 Hz

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

