



□□□□□

Eaton 267978

Eaton Z-TN Pre-selection relay, 24VAC/50Hz,
4N/O, 20A, 2HP

□□□□

PRODUCT NAME	Eaton Z-TN relay
CATALOG NUMBER	267978
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	70 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	0.263 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

□□□□

AMPERAGE RATING	20 A
MOUNTING METHOD	DIN rail
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	10.4 W
CONTROL VOLTAGE 1 TYPE	AC
AMBIENT OPERATING TEMPERATURE - MAX	45 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
CONTROL VOLTAGE 1 - MAX	24 V
CONTROL VOLTAGE 1 - MIN	24 V
CONTROL VOLTAGE 2 - MAX	0 V
CONTROL VOLTAGE 2 - MIN	0 V
FREQUENCY CONTROL VOLTAGE 1 - MAX	50 Hz
FREQUENCY CONTROL VOLTAGE 1 - MIN	50 Hz
FREQUENCY CONTROL VOLTAGE 2 - MAX	0 Hz
FREQUENCY CONTROL VOLTAGE 2 - MIN	0 Hz
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	2 W
INCANDESCENT LAMP LOAD - MAX	0 W
LOAD FLUORESCENT LAMP - MAX	0 VA
LOAD FLUORESCENT LAMP (DUO CIRCUIT) - MAX	0 VA
LOAD FLUORESCENT LAMP (PARALLEL COMPENSATED) - MAX	0 VA
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	4

□□

□□□	Z TN 2MU 4S
□□	eaton-3d-drawing-z-r-sch-einbau.jpg
	eaton-3d-drawing-r-pack.jpg
	eaton-dimensions-mas-z-tn.jpg

CONTROL VOLTAGE 2 TYPE	AC/DC
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	20 A
SUPPLY VOLTAGE - MAX	250 V
SUPPLY VOLTAGE - MIN	250 V
SWITCHING CURRENT (COS PHI = 0.6) - MAX	0 A
WIDTH IN NUMBER OF MODULAR SPACINGS	2
BUILT-IN DEPTH	60 mm
VOLTAGE TYPE	AC
FUNCTIONS	Mechanical
