



□□□□

## Eaton 269214

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 125A, B2-A125-NA

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
<b>CATALOG NUMBER</b>	269214
<b>PRODUCT LENGTH/DEPTH</b>	149 mm
<b>PRODUCT HEIGHT</b>	195 mm
<b>PRODUCT WIDTH</b>	105 mm
<b>PRODUCT WEIGHT</b>	2.4 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	CSA (File No. 22086) IEC CSA (Class No. 1432-01) Specially designed for North America CE marking CSA certified UL listed CSA-C22.2 No. 5-09 UL (Category Control Number DIVQ) UL (File No. E31593) UL 489 IEC 60947-2 IEC/EN 60947 UL/CSA



Powering Business Worldwide



<b>AMPERAGE RATING</b>	125 A
<b>VOLTAGE RATING</b>	440 V - 440 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM2
<b>FEATURES</b>	Motor drive optional Protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.



	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-038.eps</a>
	<a href="#">eaton-circuit-breaker-nzm-mccb-characteristic-curve-050.eps</a>
CHARACTERISTIC CURVE	<a href="#">eaton-circuit-breaker-current-nzm-mccb-characteristic-curve-003.eps</a>
PEP ECO-PASSPORT	<a href="#">eaton-molded-case-switches-pep-eato-00245-v0101-en.pdf</a>
	<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-019.eps</a>
	<a href="#">eaton-circuit-breaker-switch-nzm-mccb-dimensions-017.eps</a>
	<a href="#">eaton-circuit-breaker-switch-nzm-mccb-3d-drawing.eps</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FRAME</b>	NZM2
<b>POLLUTION DEGREE</b>	3
<b>LIFESPAN, MECHANICAL</b>	20000 operations
<b>UTILIZATION CATEGORY</b>	A (IEC/EN 60947-2)
<b>MOUNTING METHOD</b>	DIN rail (top hat rail) mounting optional Fixed Built-in device fixed built-in technique
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	27.61 W
<b>ISOLATION</b>	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C

<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>LOW-VOLTAGE HBC FUSE - MAX</b>	355 A gG/gL
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
<b>DEGREE OF PROTECTION</b>	IP20 (basic degree of protection, in the operating controls area) IP20
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>OVERVOLTAGE CATEGORY</b>	III
<b>RATED OPERATIONAL CURRENT</b>	300 A (380/400 V AC-1, making and breaking capacity) 300 A (415 V AC-1, making and breaking capacity)
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
<b>DEGREE OF PROTECTION (TERMINATIONS)</b>	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
<b>NUMBER OF POLES</b>	Three-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	Max. 10 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched)
<b>LIFESPAN, ELECTRICAL</b>	6500 operations at 415 V AC-3

	7500 operations at 400 V AC-1
<b>FUNCTIONS</b>	System and cable protection Current limiting circuit breaker
<b>TYPE</b>	Circuit breaker

<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity <math>I_{cn}</math>)</li> <li>• Rated current = rated uninterrupted current: 125 A</li> <li>• Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate.</li> <li>• Adjustable overload releases <math>I_r</math></li> </ul>
-------------------------	---

<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Branch circuits, feeder circuits</li> <li>• Use in unearthed supply systems at 440 V</li> </ul>
--------------------	--

<b>SHOCK RESISTANCE</b>	20 g (half-sinusoidal shock 20 ms)
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	125 A
<b>POWER LOSS</b>	27.6 W
<b>RELEASE SYSTEM</b>	Thermomagnetic release
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 10 ms
<b>SHORT-CIRCUIT RELEASE</b>	1250 A

<b>NON-DELAYED SETTING - MAX</b>	
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	750 A
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	14 mm <sup>2</sup> - 18 mm <sup>2</sup> (1x) 16 mm <sup>2</sup> - 18 mm <sup>2</sup> (2x)
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	Min. 16 mm x 5 mm direct at switch rear-side connection Max. 20 mm x 5 mm direct at switch rear-side connection M8 at rear-side screw connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	6 mm <sup>2</sup> - 11 mm <sup>2</sup> (1x) direct at switch rear-side connection 6 mm <sup>2</sup> - 12 mm <sup>2</sup> (1x) at box terminal 16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	4 mm <sup>2</sup> - 350 mm <sup>2</sup> (1x) at box terminal 4 mm <sup>2</sup> - 350 mm <sup>2</sup> (1x) at tunnel terminal 4 mm <sup>2</sup> - 3/0 mm <sup>2</sup> (1x) direct at switch rear-side connection
<b>HANDLE TYPE</b>	Rocker lever
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	1250 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	750 A
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	120
<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	125 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	100 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	30 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	25 kA

