



□□□□□

Eaton 269230

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 32A, H, frame2, A32-NA

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
CATALOG NUMBER	269230
PRODUCT LENGTH/DEPTH	149 mm
PRODUCT HEIGHT	195 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	2.419 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	CSA (File No. 22086) CSA-C22.2 No. 5-09 UL/CSA IEC/EN 60947 CSA certified UL listed Specially designed for North America UL (Category Control Number DIVQ) UL (File No. E31593) IEC 60947-2 UL 489 CE marking IEC CSA (Class No. 1432-01)



Powering Business Worldwide

AMPERAGE RATING	32 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM2
FEATURES	Motor drive optional Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

	eaton-circuit-breaker-current-nzm-mccb-characteristic-curve-005.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-040.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-050.eps
□□	eaton-circuit-breaker-nzm-mccb-dimensions-019.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device fixed built-in technique Fixed DIN rail (top hat rail) mounting optional
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	9.65 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
LOW-VOLTAGE HBC FUSE	355 A gG/gL

- MAX	
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	32 A (660-690 V AC-3, making and breaking capacity) 300 A (380/400 V AC-1, making and breaking capacity) 32 A (690 V AC -1, making and breaking capacity) 300 A (415 V AC-1, making and breaking capacity)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
DEGREE OF PROTECTION (TERMINATIONS)	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 10 segments of 16 mm x 0.8 mm at box

	terminal
LIFESPAN, ELECTRICAL	6500 operations at 400 V AC-3 10000 operations at 400 V AC-1 5000 operations at 690 V AC-3 7500 operations at 690 V AC-1 6500 operations at 415 V AC-3
FUNCTIONS	System and cable protection Current limiting circuit breaker
TYPE	Circuit breaker
SPECIAL FEATURES	• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 32 A • Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate. • Adjustable overload releases I_r
APPLICATION	• Branch circuits, feeder circuits • Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL	32 A

CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	1.9 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	1.9 kA
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	350 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	350 A
TERMINAL CAPACITY (CONTROL CABLE)	14 mm ² - 18 mm ² (1x) 16 mm ² - 18 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	M8 at rear-side screw connection Max. 20 mm x 5 mm direct at switch rear-side connection Min. 16 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	6 mm ² - 12 mm ² (1x) at box terminal 16 mm ² (1x) at tunnel terminal 6 mm ² - 11 mm ² (1x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	4 mm ² - 350 mm ² (1x) at tunnel terminal 4 mm ² - 3/0 mm ² (1x) direct at switch rear-side connection 4 mm ² - 350 mm ² (1x) at box terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	350 A
INSTANTANEOUS	350 A

CURRENT SETTING (II) - MIN	
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	32 A
OVERLOAD CURRENT SETTING (IR) - MIN	25 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	130 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	37.5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	330 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	286 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
STANDARD TERMINALS	Screw terminal
RATED OPERATING VOLTAGE UE (UL) - MAX	600Y/347 V, 480 V
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	330 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE	8000 V

(UIMP) AT MAIN
CONTACTS

RATED INSULATION
VOLTAGE (UI)

1000 V AC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the
latest product and support
information.

