



□□□□□

Eaton 271428

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM2, 3 pole, Icu 400/415 V 50 Hz(Icu): 36 kA, 160 A, Fixed, Screw connection, IEC

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker magnetic
CATALOG NUMBER	271428
PRODUCT LENGTH/DEPTH	149 mm
PRODUCT HEIGHT	184 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	2.345 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC



Powering Business Worldwide

AMPERAGE RATING	160 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM2

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF PROTECTION OF

Does not apply, since the entire switchgear needs to

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
LIFESPAN, MECHANICAL	20000 operations
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	38.4 W
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
DEGREE OF PROTECTION	IP20 (basic degree of protection, in the operating controls area) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
OVERVOLTAGE	III

CATEGORY	
RATED OPERATIONAL CURRENT	134 A (400 V AC-3, making and breaking capacity)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 24 mm x 0.8 mm at rear-side connection (punched) Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal
LIFESPAN, ELECTRICAL	10000 operations at 400 V AC-1 5000 operations at 690 V AC-1 7500 operations at 415 V AC-1
FUNCTIONS	Short-circuit protection
TYPE	Circuit breaker
SPECIAL FEATURES	• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Motor protection in conjunction with overload relay • With short-circuit release • Without overload release I_r • IEC/EN 60947-4-1, IEC/EN 60947-2

	• The circuit-breaker fulfills all requirements for AC-3 switching category. • Rated current = rated uninterrupted current: 160 A
APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 1.5 mm ² (2x) 0.75 mm ² - 2.5 mm ² (1x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 24 mm x 8 mm direct at switch rear-side connection M8 at rear-side screw connection Min. 16 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	6 mm ² - 16 mm ² (2x) at box terminal 16 mm ² (1x) at tunnel terminal 6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 10 mm ² - 16 mm ² (1x) at box terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 70 mm ² (2x) at box terminal 25 mm ² - 70 mm ² (2x) direct at switch rear-side connection 25 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 185 mm ² (1x) at box terminal 25 mm ² - 185 mm ² (1x) direct at switch rear-side connection

