

Eaton 271449

Eaton Moeller series NZM - Molded Case Circuit Breaker. Door coupling rotary handle red-yellow, size 1, NA type

PRODUCT NAME	Eaton Moeller series NZM operating element NA
CATALOG NUMBER	271449
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	190 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.627 kg
COMPLIANCES	IEC UL/CSA RoHS conform
CERTIFICATIONS	UL (File No. E140305) CE marking UL listed UL489 UL (Category Control Number DIHS) CSA (File No. 22086) IEC60947 CSA (Class No. 1437-01) CSA-C22.2 No. 5-09 CSA certified

USED WITH	NZM1, N(S)1
FEATURES	Red-yellow for emergency switching off Lockable
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product

eaton-circuit-breaker-door-nzm-rotary-handle-dimensions-010.eps
eaton-circuit-breaker-door-nzm-rotary-handle-dimensions-005.eps
eaton-circuit-breaker-door-nzm-rotary-handle-3d-drawing-004.eps

	standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
COLOR	Red
FITTED WITH:	Padlock
FRAME	NZM1
SUITABLE FOR	Power circuit breaker Emergency stop Switch disconnecter
COVER/DOOR TYPE	Door interlock not defeated in the locked OFF position. Door opens only with active rotation beyond the 0 position
LOCK NUMBER	Double lockable
LOCKING FACILITY	With door interlock Lockable on the handle on the switch using up to 3 padlocks
TYPE	<ul style="list-style-type: none"> • Accessory • Door coupling rotary handle
SPECIAL FEATURES	<ul style="list-style-type: none"> • Complete including

- rotary drive and coupling parts
- Extension shaft additionally required.
- Cannot be combined with mechanical interlock
- External warning plate/designation label can be clipped on.
- Door coupling rotary handle for operating the switch through a closed control panel door

DEGREE OF PROTECTION IP66
/ NEMA ENCLOSURE TYPE 4X, 12

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

