



□□□□

Eaton 271454

Eaton Moeller series NZM - Molded Case Circuit Breaker. Rotary handle, black, lockable on the handle, NA type

□□□□

PRODUCT NAME	Eaton Moeller series NZM operating element NA
CATALOG NUMBER	271454
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	0.33 kg
COMPLIANCES	IEC UL/CSA RoHS conform
CERTIFICATIONS	CSA (File No. 22086) UL listed CSA-C22.2 No. 5-09 CSA (Class No. 1437-01) UL (File No. E140305) CE marking CSA certified UL489 UL (Category Control Number DIHS) IEC60947



Powering Business Worldwide

USED WITH	NZM2, N(S)2
FEATURES	Lockable Standard: black / gray
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.

[eaton-circuit-breaker-nzm-rotary-handle-dimensions-006.eps](#)

[eaton-circuit-breaker-rotary-handle-nzm-rotary-handle-dimensions-002.eps](#)

[eaton-circuit-breaker-rotary-handle-nzm-rotary-handle-3d-drawing.eps](#)

10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
COLOR	Black
FITTED WITH:	Padlock
FRAME	NZM2
SUITABLE FOR	Switch disconnecter Power circuit breaker
COVER/DOOR TYPE	Door interlock not defeated in the locked OFF and ON positions Door opens only with active rotation beyond the 0 position Door interlock can be defeated from the outside using a 1 mm pin Door interlock cannot be combined with mechanical locking Door interlock in ON position Door interlock can only be switched ON when the door is closed
LOCKING FACILITY	Can also be modified in I position Lockable on the 0 position on the handle using up to 3 padlocks Also available with door interlock e.g. for MCC service distribution
TYPE	Rotary handle on switch with door interlock

