

Eaton 272250

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 80A, B1-AF80-NA

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
CATALOG NUMBER	272250
PRODUCT LENGTH/DEPTH	88 mm
PRODUCT HEIGHT	165.5 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	1.072 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	CSA (File No. 22086) IEC 60947-2 UL 489 UL (Category Control Number DIVQ) UL listed CSA-C22.2 No. 5-09 UL (File No. E31593) CSA (Class No. 1432-01) CE marking UL/CSA IEC/EN 60947 Specially designed for North America IEC CSA certified

AMPERAGE RATING	80 A
VOLTAGE RATING	440 V - 440 V
CIRCUIT BREAKER FRAME TYPE	NZM1
FEATURES	Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.

CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-036.eps
	eaton-circuit-breaker-nzm-mccb-characteristic-curve-051.eps
	eaton-circuit-breaker-current-nzm-mccb-characteristic-curve.eps
	eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf
	eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps
	eaton-circuit-breaker-nzm-mccb-dimensions-017.eps
	eaton-circuit-breaker-switch-nzm-mccb-3d-drawing-006.eps

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	16.32 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C

AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
LOW-VOLTAGE HBC FUSE - MAX	200 A gG/gL
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 (basic degree of protection, in the operating controls area) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Frame clamp
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	160 A (380/400 V AC-1, making and breaking capacity) 125 A (415 V AC-1, making and breaking capacity)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP00 (terminations, phase isolator and strip terminal) IP10 (tunnel terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 9 segments of 9 mm x 0.8 mm at box terminal
LIFESPAN, ELECTRICAL	7500 operations at 400 V AC-1

FUNCTIONS	System and cable protection Current limiting circuit breaker
TYPE	Circuit breaker
SPECIAL FEATURES	• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 80 A • Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate. • Fixed overload releases I_r
APPLICATION	• Branch circuits, feeder circuits • Use in unearthed supply systems at 440 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	80 A
POWER LOSS	16.3 W
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
SHORT-CIRCUIT RELEASE	800 A

NON-DELAYED SETTING - MAX	
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	480 A
TERMINAL CAPACITY (CONTROL CABLE)	14 mm ² - 18 mm ² (1x) 16 mm ² - 18 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	M8 at rear-side screw connection Max. 16 mm x 5 mm direct at switch rear-side connection Min. 12 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	6 mm ² - 12 mm ² (1x) at box terminal 6 mm ² - 12 mm ² (1x) direct at switch rear-side connection 16 mm ² - 95 mm ² (1x) at tunnel terminal 6 mm ² - 9 mm ² (2x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	4 mm ² - 2/0 mm ² (1x) direct at switch rear-side connection 25 mm ² - 70 mm ² (1x) at box terminal 4 mm ² - 3/0 mm ² (1x) at tunnel terminal 25 mm ² (2x) at box terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	800 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	480 A
NUMBER OF OPERATIONS PER HOUR - MAX	120

OVERLOAD CURRENT SETTING (IR) - MAX	80 A
OVERLOAD CURRENT SETTING (IR) - MIN	80 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	30 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	25 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	18.5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	53 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	53 kA
STANDARD TERMINALS	Box terminal
RATED OPERATING VOLTAGE UE (UL) - MAX	480 Y / 277 V
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	63 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	6000 V
RATED INSULATION VOLTAGE (UI)	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

