

Eaton 276569

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 3 kW, 1 N/O, 220 V DC, DC operation, Screw terminals

| | |
|-----------------------------|---|
| | |
| PRODUCT NAME | Eaton Moeller® series DILM contactor |
| CATALOG NUMBER | 276569 |
| PRODUCT LENGTH/DEPTH | 75 mm |
| PRODUCT HEIGHT | 68 mm |
| PRODUCT WIDTH | 45 mm |
| PRODUCT WEIGHT | 0.296 kg |
| COMPLIANCES | CE Marked |
| CERTIFICATIONS | UL 508 VDE IEC/EN 60947-4-1 UL File No.: E29096 CSA Class No.: 2411-03, 3211-04 VDE 0660 UL CSA UL Category Control No.: NLDX CE CSA File No.: 012528 IEC/EN 60947 CSA-C22.2 No. 60947-4-1-14 |
| CATALOG NOTES | Contacts according to EN 50012 |

| | | |
|---|--|------------------|
| ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT | | Screw connection |
| AMPERAGE RATING | 7A | |
| NUMBER OF POLES | Three-pole | |
| VOLTAGE RATING | 220 Vdc | |
| 10.10 TEMPERATURE RISE | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. | |
| 10.11 SHORT-CIRCUIT RATING | Is the panel builder's responsibility. The specifications for the switchgear must be observed. | |
| 10.12 ELECTROMAGNETIC COMPATIBILITY | Is the panel builder's responsibility. The specifications for the switchgear must be observed. | |
| 10.13 MECHANICAL FUNCTION | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. | |
| 10.2.2 CORROSION RESISTANCE | Meets the product standard's requirements. | |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES | Meets the product standard's requirements. | |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT | Meets the product standard's requirements. | |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements. | |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION | Meets the product standard's requirements. | |
| 10.2.5 LIFTING | Does not apply, since the entire switchgear needs to be evaluated. | |

| | |
|-----------------------------------|--|
| CHARACTERISTIC CURVE | eaton-contactors-switch-dilm-characteristic-curve-002.eps eaton-contactors-switch-dilm-characteristic-curve.eps |
| DECLARATIONS OF CONFORMITY | eaton-contactor-declaration-of-conformity-uk251209en.pdf eaton-contactors-dila-dilm7-15-dilmp20-il03407013z.pdf |
| | eaton-contactors-contact-dilm-wiring-diagram.eps eaton-contactors-frame-dilm-dimensions.eps eaton-contactors-module-dilm-dimensions-002.eps eaton-contactors-module-dilm-dimensions.eps eaton-contactors-dilm-3d-drawing-007.eps |

| | |
|---|---|
| 10.2.6 MECHANICAL IMPACT | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 INSCRIPTIONS | Meets the product standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| FITTED WITH: | Varistor suppressor circuit |
| OPERATING FREQUENCY | 9000 mechanical Operations/h (DC operated) |
| POLLUTION DEGREE | 3 |
| CLIMATIC PROOFING | Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78 |
| CONNECTION TO SMARTWIRE-DT | No |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) | 8000 V AC |
| UTILIZATION CATEGORY | AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-3: Normal AC induction motors: starting, switch off during running AC-1: Non-inductive or |

| | |
|--|--|
| | slightly inductive loads, resistance furnaces |
| CONNECTION | Screw terminals |
| FRAME SIZE | FS1 |
| AMBIENT OPERATING TEMPERATURE - MAX | 60 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -25 °C |
| AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX | 40 °C |
| AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN | -25 °C |
| AMBIENT STORAGE TEMPERATURE - MAX | 80 °C |
| AMBIENT STORAGE TEMPERATURE - MIN | -40 °C |
| ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE | 0.25 HP |
| ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE | 1.5 HP |
| ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE | 1 HP |
| ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE | 2 HP |
| ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE | 3 HP |
| ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE | 5 HP |
| CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED) | 45 A |
| CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED) | 18 A |
| CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN) | 21 A |
| CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1- POLE, OPEN) | 50 A |

| | |
|---|--|
| EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID | 0.3 W |
| HEAT DISSIPATION CAPACITY PDISS | 0 W |
| HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID | 0.1 W |
| SWITCHING TIME (DC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX | 31 ms |
| SWITCHING TIME (DC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX | 12 ms |
| APPLICATION | Contactors for Motors |
| PRODUCT CATEGORY | Contactors |
| PROTECTION | Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274) |
| ARCING TIME | 10 ms |
| ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT | Screw connection |
| SCREWDRIVER SIZE | 0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver |
| VOLTAGE TYPE | DC |
| DEGREE OF PROTECTION | IP20 |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS) | 0 |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS) | 1 |
| NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT | 0 |
| NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS) | 1 |
| NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT) | 3 |

| | |
|---|--|
| OPERATING TEMPERATURE - MAX | 60 °C |
| OPERATING TEMPERATURE - MIN | -25 °C |
| POWER CONSUMPTION (PICK-UP) AT DC | 3 W |
| POWER CONSUMPTION (SEALING) AT DC | 3 W |
| RATED BREAKING CAPACITY AT 220/230 V | 70 A |
| RATED BREAKING CAPACITY AT 380/400 V | 70 A |
| RATED BREAKING CAPACITY AT 500 V | 50 A |
| RATED BREAKING CAPACITY AT 660/690 V | 40 A |
| RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX | 0 V |
| RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN | 0 V |
| RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX | 0 V |
| RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN | 0 V |
| CONTACT CONFIGURATION | 1 NO |
| DROP-OUT VOLTAGE | 0.6 - 0.15 x UC, DC operated At least smoothed two-phase bridge rectifier or three-phase rectifier |
| OVERVOLTAGE CATEGORY | III |
| DUTY FACTOR | 100 % |
| EMITTED INTERFERENCE | According to EN 60947-1 |
| INTERFERENCE IMMUNITY | According to EN 60947-1 |
| LIFESPAN, MECHANICAL | 10,000,000 Operations (DC operated) |
| PICK-UP VOLTAGE | 0.85 - 1.1 V DC x Uc (only with auxiliary contact module with 3 or more N/C contacts) 0.8 - 1.1 V DC x Uc |

| | |
|---|---|
| SAFE ISOLATION | 400 V AC, Between the contacts, According to EN 61140 400 V AC, Between coil and contacts, According to EN 61140 |
| SCREW SIZE | M3.5, Terminal screw |
| SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE) | 10 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA) |
| SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY) | A600, AC operated (UL/CSA) P300, DC operated (UL/CSA) |
| TERMINAL CAPACITY (FLEXIBLE WITH FERRULE) | 2 x (0.75 - 2,5) mm ² 1 x (0.75 - 2.5) mm ² |
| SHOCK RESISTANCE | 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 3.4 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 5.7 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 3.4 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms |
| TERMINAL CAPACITY (SOLID) | 1 x (0.75 - 4) mm ² 2 x (0.75 - 2.5) mm ² |
| TERMINAL CAPACITY (SOLID/STRANDED AWG) | Single 18 - 10, double 18 - 14 |
| SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE) | 20 A, Maximum motor rating (UL/CSA) |

| | |
|--|-------------------------|
| TIGHTENING TORQUE | 1.2 Nm, Screw terminals |
| RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX | 220 V |
| RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN | 220 V |
| RATED INSULATION VOLTAGE (UI) | 690 V |
| RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947) | 112 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V | 22 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V | 7 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V | 7 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V | 7 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V | 5 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V | 4 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V | 5 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V | 5 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V | 5 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V | 4.5 A |
| RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V | 4 A |
| RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V | 20 A |
| RATED OPERATIONAL | 15 A |

| | |
|--|--------|
| CURRENT (IE) AT DC-1, 220 V | |
| RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V | 20 A |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 7 A |
| RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ | 2.2 kW |
| RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ | 3 kW |
| RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ | 4 kW |
| RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ | 1 kW |
| RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ | 1.5 kW |
| RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ | 2.2 kW |
| RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ | 2.3 kW |
| RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ | 2.4 kW |
| RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ | 2.5 kW |
| RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ | 2.9 kW |
| RATED OPERATIONAL POWER (NEMA) | 2.2 kW |
| RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX | 690 V |
| RESISTANCE PER POLE | 4.6 mΩ |
| STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS | 3 W |
| STRIPPING LENGTH (CONTROL CIRCUIT) | 10 mm |

| | |
|---|--|
| CABLE) | |
| STRIPPING LENGTH (MAIN CABLE) | 10 mm |
| SHORT-CIRCUIT CURRENT RATING (BASIC RATING) | 5 kA, 25 A max. fuse, SCCR (UL/CSA) 5 kA, 25 A max. CB, SCCR (UL/CSA) |
| SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V) | 100 kA, 20 A CLASS J max. fuse, SCCR (UL/CSA) 30 kA, 25 A CLASS RK5 max. fuse, SCCR (UL/CSA) 65 kA, 16 A max. CB, SCCR (UL/CSA) |
| SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V) | 100 kA, 20 A CLASS J max. fuse, SCCR (UL/CSA) 30 kA, 25 A CLASS RK5 max. fuse, SCCR (UL/CSA) |
| SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V | 35 A gG/gL |
| SUITABLE FOR | Also motors with efficiency class IE3 |
| SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V | 20 A gG/gL |
| SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V | 20 A gG/gL |
| SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V | 16 A gG/gL |
| SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS | 12 A (600V 60Hz 3phase, 347V 60Hz 1phase) 12 A (480V 60Hz 3phase, 277V 60Hz 1phase) |
| SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING | 42 A, LRA 480 V 60 Hz 3- ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 7 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) |
| SPECIAL PURPOSE RATING OF ELEVATOR CONTROL | 0.75 HP, 200 V 60 Hz 3-ph, (UL/CSA) 2 HP, 480 V 60 Hz 3-ph, (UL/CSA) 3.4 A, 480 V 60 Hz 3-ph, (UL/CSA) 3 HP, 600 V 60 Hz 3-ph, |

| | |
|---|---|
| | (UL/CSA) 3.7 A, 200 V 60 Hz 3-ph, (UL/CSA) 6 A, 240 V 60 Hz 3-ph, (UL/CSA) 3.9 A, 600 V 60 Hz 3-ph, (UL/CSA) 1.5 HP, 240 V 60 Hz 3-ph, (UL/CSA) |
| SPECIAL PURPOSE RATING OF REFRIGERATION CONTROL (CSA ONLY) | 60 A, LRA 480 V 60 Hz 3phase; (CSA) 10 A, FLA 480 V 60 Hz 3phase; (CSA) 60 A, LRA 600 V 60 Hz 3phase; (CSA) 10 A, FLA 600 V 60 Hz 3phase; (CSA) |
| SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING | 12 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 12 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) |
| SPECIAL PURPOSE RATING OF TUNGSTEN INCANDESCENT LAMPS | 14 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 14 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) |
| OPERATING TEMPERATURE | -25° to 60°C |
| CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN) | 22 A |
| CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN) | 21 A |
| CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN) | 20 A |
| RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ | 4.5 kW |
| RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ | 3.5 kW |
| RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ | 3.5 kW |
| ACTUATING VOLTAGE | 220 V DC |
| ALTITUDE | Max. 2000 m |

| | |
|---|-------|
| OPERATING VOLTAGE AT AC, 50 HZ - MIN | 24 V |
| OPERATING VOLTAGE AT AC, 50 HZ - MAX | 690 V |
| OPERATING VOLTAGE AT AC, 60 HZ - MIN | 24 V |
| OPERATING VOLTAGE AT AC, 60 HZ - MAX | 690 V |

| |
|------------------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

