

Eaton 277779

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 18.5 kW, *V 60 Hz, AC operation, Screw terminals

PRODUCT NAME	Eaton Moeller® series DILM contactor
CATALOG NUMBER	277779
PRODUCT LENGTH/DEPTH	132.1 mm
PRODUCT HEIGHT	115 mm
PRODUCT WIDTH	55 mm
PRODUCT WEIGHT	0.872 kg
CERTIFICATIONS	CSA-C22.2 No. 60947-4-1-14 UL UL File No.: E29096 VDE 0660 CE CSA File No.: 012528 IEC/EN 60947 IEC/EN 60947-4-1 CSA UL 60947-4-1 UL Category Control No.: NLDX CSA Class No.: 2411-03, 3211-04
CATALOG NOTES	Contacts according to EN 50012

NUMBER OF POLES	Three-pole
VOLTAGE RATING	400 V
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

CHARACTERISTIC CURVE	eaton-contactors-switch-dilm-characteristic-curve.eps
	eaton-contactors-switch-dilm-characteristic-curve-002.eps
	IL03407033Z
	eaton-contactors-contact-dilm-wiring-diagram-003.eps
	eaton-contactors-dilm-dimensions-002.eps

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FREQUENCY RATING	60 Hz
OPERATING FREQUENCY	5000 mechanical Operations/h (AC operated)
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8000 V AC
UTILIZATION CATEGORY	AC-3: Normal AC induction motors: starting, switch off during running AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-4: Normal AC induction motors: starting, plugging, reversing, inching
CONNECTION	Screw terminals
FRAME SIZE	FS3
AMBIENT OPERATING	60 °C

TEMPERATURE - MAX	
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	3 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	10 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	7.5 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	30 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	40 HP
CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)	112 A
CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)	45 A
CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)	55 A
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)	125 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	6.6 W
HEAT DISSIPATION CAPACITY PDISS	0 W

HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	2.2 W
APPLICATION	Contactors for Motors
PRODUCT CATEGORY	Contactors
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
ARCING TIME	10 ms
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
SCREWDRIVER SIZE	0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
VOLTAGE TYPE	AC
DEGREE OF PROTECTION	IP00
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT	0
NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)	3
RATED BREAKING CAPACITY AT 220/230 V	400 A
RATED BREAKING CAPACITY AT 380/400 V	400 A
RATED BREAKING CAPACITY AT 500 V	400 A
RATED BREAKING CAPACITY AT 660/690 V	250 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60	600 V

HZ - MAX	
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	24 V
DROP-OUT VOLTAGE	AC operated: 0.6 - 0.3 x U _C , AC operated
OVERVOLTAGE CATEGORY	III
DUTY FACTOR	100 %
EMITTED INTERFERENCE	According to EN 60947-1
INTERFERENCE IMMUNITY	According to EN 60947-1
LIFESPAN, MECHANICAL	10,000,000 Operations (AC operated)
PICK-UP VOLTAGE	0.8 - 1.1 V AC x U _C
POWER CONSUMPTION, PICK-UP, 50 HZ	149 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140 440 V AC, Between coil and contacts, According to EN 61140
POWER CONSUMPTION, PICK-UP, 60 HZ	178 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz
SCREW SIZE	M3.5, Terminal screw, Control circuit cables M6, Terminal screw, Main cables
POWER CONSUMPTION, SEALING, 50 HZ	4.1 W, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz 16 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz
POWER CONSUMPTION, SEALING, 60 HZ	19 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz 4.1 W, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz
TERMINAL CAPACITY (STRANDED)	1 x (16 - 50) mm ² , Main cables 2 x (16 - 35) mm ² , Main cables
TERMINAL CAPACITY (COPPER BAND)	2 x (6 x 9 x 0.8) mm (Number of segments x width x thickness), Main

	cables
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 35) mm ² , Main cables 1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 25) mm ² , Main cables
SHOCK RESISTANCE	7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half- sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half- sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half- sinusoidal shock 10 ms
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 16) mm ² , Main cables 1 x (0.75 - 4) mm ² , Control circuit cables 2 x (0.75 - 16) mm ² , Main cables 2 x (0.75 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14, Control circuit cables Single 14 - 1, double 14 - 2, Main cables
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	63 A, Maximum motor rating (UL/CSA)
POWER CONSUMPTION	18.5 kW
TIGHTENING TORQUE	3.3 Nm, Screw terminals, Main cables

	1.2 Nm, Screw terminals, Control circuit cables
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED INSULATION VOLTAGE (UI)	690 V
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947)	560 A
RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V	60 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	25 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V	14 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V	50 A

RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V	45 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V	50 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	40 A
RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ	13.5 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	18.5 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	24 kW
RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ	5 kW
RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ	9 kW
RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ	9.5 kW
RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ	10 kW
RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ	11 kW
RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ	12 kW
RATED OPERATIONAL POWER (NEMA)	22 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RESISTANCE PER POLE	1.9 mΩ
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	4.1 W
STRIPPING LENGTH	10 mm

(CONTROL CIRCUIT CABLE)	
STRIPPING LENGTH (MAIN CABLE)	14 mm
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	18 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN	12 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	13 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN	8 ms
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	10 kA, SCCR (UL/CSA) 250 A, max. Fuse, SCCR (UL/CSA) 250 A, max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)	250/150 A, Class J, max. Fuse, SCCR (UL/CSA) 30/100 kA, Fuse, SCCR (UL/CSA) 65 kA, CB, SCCR (UL/CSA) 100 A, max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)	30 kA, CB, SCCR (UL/CSA) 250/150 A, Class J, max. Fuse, SCCR (UL/CSA) 250 A, max. CB, SCCR (UL/CSA) 30/100 kA, Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V	125 A gG/gL
SUITABLE FOR	Also motors with efficiency class IE3
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V	80 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION)	63 A gG/gL

AT 400 V	
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V	50 A gG/gL
SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS	79 A (600V 60Hz 3phase, 347V 60Hz 1phase) 79 A (480V 60Hz 3phase, 277V 60Hz 1phase)
SPECIAL PURPOSE RATING OF ELEVATOR CONTROL	25.3 A, 200 V 60 Hz 3-ph, (UL/CSA) 7.5 HP, 200 V 60 Hz 3-ph, (UL/CSA) 10 HP, 240 V 60 Hz 3-ph, (UL/CSA) 34 A, 480 V 60 Hz 3-ph, (UL/CSA) 28 A, 240 V 60 Hz 3-ph, (UL/CSA) 25 HP, 480 V 60 Hz 3-ph, (UL/CSA) 30 HP, 600 V 60 Hz 3-ph, (UL/CSA) 32 A, 600 V 60 Hz 3-ph, (UL/CSA)
SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING	79 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 79 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
SPECIAL PURPOSE RATING OF TUNGSTEN INCANDESCENT LAMPS	74 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 74 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)
CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)	60 A
CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)	57 A
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	50 A
RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ	25 kW
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	28 kW

RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	23 kW
ACTUATING VOLTAGE	*V 60 Hz
ALTITUDE	Max. 2000 m
OPERATING VOLTAGE AT AC, 50 HZ - MIN	230 V
OPERATING VOLTAGE AT AC, 50 HZ - MAX	690 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	230 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	690 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

