



□□□□□

Eaton 278459

Eaton Moeller® series ZB Overload relay,
ZB65, Ir= 40 - 57 A, 1 N/O, 1 N/C, Direct
mounting, IP00

□□□□

PRODUCT NAME	Eaton Moeller® series ZB Thermal overload relay
CATALOG NUMBER	278459
UPC	782116358878
PRODUCT LENGTH/DEPTH	88 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	60 mm
PRODUCT WEIGHT	0.23 kg
CERTIFICATIONS	CSA File No.: 012528 UL Category Control No.: NKCR UL 60947-4-1 UL File No.: E29184 VDE 0660 CSA-C22.2 No. 60947-4-1- 14 CSA IEC/EN 60947 UL IEC/EN 60947-4-1 CE CSA Class No.: 3211-03

FEATURES

Phase-failure sensitivity
(according to IEC/EN
60947, VDE 0660 Part 102)
Test/off button
Reset pushbutton
manual/auto

10.10 TEMPERATURE RISE

The panel builder is
responsible for the
temperature rise
calculation. Eaton will
provide heat dissipation
data for the devices.

**10.11 SHORT-CIRCUIT
RATING**

Is the panel builder's
responsibility. The
specifications for the
switchgear must be
observed.

**10.12 ELECTROMAGNETIC
COMPATIBILITY**

Is the panel builder's
responsibility. The
specifications for the
switchgear must be
observed.

**10.13 MECHANICAL
FUNCTION**

The device meets the
requirements, provided
the information in the
instruction leaflet (IL) is
observed.

**10.2.2 CORROSION
RESISTANCE**

Meets the product
standard's requirements.

**10.2.3.1 VERIFICATION OF
THERMAL STABILITY OF
ENCLOSURES**

Meets the product
standard's requirements.

**10.2.3.2 VERIFICATION OF
RESISTANCE OF
INSULATING MATERIALS
TO NORMAL HEAT**

Meets the product
standard's requirements.

**10.2.3.3 RESIST. OF
INSUL. MAT. TO
ABNORMAL HEAT/FIRE
BY INTERNAL ELECT.
EFFECTS**

Meets the product
standard's requirements.

**10.2.4 RESISTANCE TO
ULTRA-VIOLET (UV)
RADIATION**

Meets the product
standard's requirements.

10.2.5 LIFTING

Does not apply, since the
entire switchgear needs to
be evaluated.

**10.2.6 MECHANICAL
IMPACT**

Does not apply, since the
entire switchgear needs to
be evaluated.

10.2.7 INSCRIPTIONS

Meets the product
standard's requirements.

CHARACTERISTIC CURVE

[eaton-tripping-devices-
characteristic-zb-overload-
relay-characteristic-curve-
005.eps](#)

**DECLARATIONS OF
CONFORMITY**

[eaton-thermal-overload-
relay-declaration-of-
conformity-
uk251269en.pdf](#)

MCAD MODEL

[zb65.stp](#)

□□□□□

[eaton-overload-relay-
zb65-il03407008z.pdf](#)

□□

[eaton-tripping-devices-
overload-relay-zb-
overload-relay-
dimensions-002.eps](#)

[eaton-tripping-devices-
overload-relay-zb-
overload-relay-
dimensions-005.eps](#)

[eaton-tripping-devices-
overload-relay-zb-
overload-relay-3d-
drawing-003.eps](#)

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
CLASS	CLASS 10 A
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V (auxiliary and control circuits) 6000 V AC
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	1.5 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	0.9 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.4 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.2 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	0.9 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 60 V	0.75 A
RATED OPERATIONAL	57 A

CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
STRIPPING LENGTH (CONTROL CIRCUIT CABLE)	8 mm
STRIPPING LENGTH (MAIN CABLE)	11 mm
VOLTAGE RATING - MAX	600 VAC
PRODUCT CATEGORY	<ul style="list-style-type: none"> • Accessories • Overload relay ZB up to 150 A
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
FRAME SIZE	ZB65
ADJUSTABLE CURRENT RANGE - MAX	57 A
ADJUSTABLE CURRENT RANGE - MIN	40 A
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	25 °C
CONVENTIONAL THERMAL CURRENT ITH OF AUXILIARY CONTACTS (1-POLE, OPEN)	6 A
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	12.9 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	4.3 W
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	0

NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
OVERLOAD RELEASE CURRENT SETTING - MAX	57 A
OVERLOAD RELEASE CURRENT SETTING - MIN	40 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	690 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 120 V	1.5 A
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
RESET FUNCTION	Automatic Push-button
SCREWDRIVER SIZE	2, Terminal screw, Pozidriv screwdriver 1 x 6 mm, Terminal screw, Standard screwdriver
MOUNTING METHOD	Direct mounting Direct attachment
DEGREE OF PROTECTION	IP00
OVERVOLTAGE CATEGORY	III
SAFE ISOLATION	440 V, Between auxiliary contacts and main contacts, According to EN 61140 440 V AC, Between main circuits, According to EN 61140 240 V AC, Between auxiliary contacts, According to EN 61140
SCREW SIZE	M3.5, Terminal screw, Control circuit cables M6, Terminal screw, Main cables
SHOCK RESISTANCE	10 g, Mechanical, Sinusoidal, Shock duration 10 ms
SHORT-CIRCUIT CURRENT	10 kA, SCCR (UL/CSA)

RATING (BASIC RATING)	150 A, max. CB, SCCR (UL/CSA) 200 A, max. Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)	100 A, Class J, max. Fuse, SCCR (UL/CSA) 75 A, max. CB, SCCR (UL/CSA) 65 kA, CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)	100 kA, Fuse, SCCR (UL/CSA) 110 A, Class J/CC, max. Fuse, SCCR (UL/CSA)
TERMINAL CAPACITY (STRANDED)	1 x (16 - 25) mm ² , Main cables
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	R300, DC operated (UL/CSA) B300 at opposite polarity, AC operated (UL/CSA) B600 at opposite polarity, AC operated (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING	Max. 6 A gG/gL, fuse, Without welding, Auxiliary and control circuits 80 A gG/gL, Fuse, Type "2" coordination 160 A gG/gL, Fuse, Type "1" coordination
SUITABLE FOR	Branch circuits, (UL/CSA)
TEMPERATURE COMPENSATION	≤ 0.25 %/K, residual error for T > 40° Continuous
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (1 - 25) mm ² , Main cables 1 x (1 - 25) mm ² , Main cables
TERMINAL CAPACITY (SOLID)	2 x (1 - 16) mm ² , Main cables 1 x (0.75 - 4) mm ² , Control circuit cables 2 x (0.75 - 4) mm ² , Control circuit cables 1 x (1 - 16) mm ² , Main cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	2 x (18 - 14), Control circuit cables 14 - 2, Main cables
TIGHTENING TORQUE	3.5 Nm, Screw terminals, Main cables 1.2 Nm, Screw terminals, Control circuit cables

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

