



□□□□

## Eaton 276853

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 5.5 kW, 1 NC, 48 V 50 Hz, AC operation, Screw terminals

□□□□

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton Moeller® series DILM contactor   |
| <b>CATALOG NUMBER</b>       | 276853   |
| <b>PRODUCT LENGTH/DEPTH</b> | 75 mm  |
| <b>PRODUCT HEIGHT</b>       | 68 mm  |
| <b>PRODUCT WIDTH</b>        | 45 mm  |
| <b>PRODUCT WEIGHT</b>       | 0.24 kg  |
| <b>COMPLIANCES</b>          | CE Marked  |
| <b>CERTIFICATIONS</b>       | UL 508<br>VDE<br>UL<br>CE<br>CSA-C22.2 No. 14-05<br>IEC/EN 60947<br>IEC/EN 60947-4-1<br>UL Category Control No.: NLDX<br>CSA File No.: 012528<br>VDE 0660<br>UL File No.: E29096<br>CSA<br>CSA Class No.: 2411-03, 3211-04 |
| <b>CATALOG NOTES</b>        | Contacts according to EN 50012   |



Powering Business Worldwide

|   |  |
|---|--|
| <b>ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT</b>            | Screw connection   |
| <b>AMPERAGE RATING</b>  | 12A  |
| <b>NUMBER OF POLES</b>  | Three-pole   |
| <b>VOLTAGE RATING</b>   | 48 V   |
| <b>10.10 TEMPERATURE RISE</b>   | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>   | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>  | Meets the product standard's requirements.   |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.   |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.   |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.   |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | Meets the product standard's requirements.   |
| <b>10.2.5 LIFTING</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.2.6 MECHANICAL IMPACT</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |

|                                   |  |
|-----------------------------------|--|
| <b>CHARACTERISTIC CURVE</b>       | <a href="#">eaton-contactors-switch-dilm-characteristic-curve-002.eps</a><br><a href="#">eaton-contactors-switch-dilm-characteristic-curve.eps</a>   |
| <b>DECLARATIONS OF CONFORMITY</b> | <a href="#">eaton-contactor-declaration-of-conformity-uk251209en.pdf</a>   |
| □□□□□                             | <a href="#">eaton-contactors-dila-dilm7-15-dilmp20-il03407013z.pdf</a>   |
| □□                                | <a href="#">eaton-contactors-frame-dilm-dimensions.eps</a><br><a href="#">eaton-contactors-module-dilm-dimensions-002.eps</a><br><a href="#">eaton-contactors-module-dilm-dimensions.eps</a><br><a href="#">eaton-contactors-dilm-3d-drawing-007.eps</a> |

|   |   |
|---|---|
| <b>10.2.7 INSCRIPTIONS</b>                                      | Meets the product standard's requirements.  |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.  |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.  |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.  |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.  |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.  |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.  |
| <b>FITTED WITH:</b>   | Mirror contact  |
| <b>FREQUENCY RATING</b>   | 50 Hz   |
| <b>OPERATING FREQUENCY</b>                                      | 9000 mechanical Operations/h (AC operated)  |
| <b>POLLUTION DEGREE</b>   | 3   |
| <b>UTILIZATION CATEGORY</b>                                     | AC-1: Non-inductive or slightly inductive loads, resistance furnaces<br>AC-4: Normal AC induction motors: starting, plugging, reversing, inching<br>AC-3: Normal AC induction motors: starting, switch off during running |
| <b>CLIMATIC PROOFING</b>  | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30  |
| <b>CONNECTION TO SMARTWIRE-DT</b>                               | No  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 8000 V AC   |
| <b>CONNECTION</b>   | Screw terminals   |
| <b>FRAME SIZE</b>   | FS1   |

|   |        |
|---|--------|
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                              | 60 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                              | -25 °C |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>                   | 40 °C  |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>                   | -25 °C |
| <b>AMBIENT STORAGE TEMPERATURE - MAX</b>                                | 80 °C  |
| <b>AMBIENT STORAGE TEMPERATURE - MIN</b>                                | -40 °C |
| <b>ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE</b>                | 1 HP   |
| <b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE</b>                | 3 HP   |
| <b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE</b>                | 2 HP   |
| <b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE</b>                | 3 HP   |
| <b>ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE</b>                | 10 HP  |
| <b>ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE</b>                | 10 HP  |
| <b>CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)</b>              | 45 A   |
| <b>CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)</b>              | 18 A   |
| <b>CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)</b>          | 21 A   |
| <b>CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)</b> | 50 A   |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>               | 0 W    |
| <b>HEAT DISSIPATION CAPACITY PDISS</b>                                  | 0 W    |
| <b>HEAT DISSIPATION PER POLE, CURRENT-</b>                              | 0.3 W  |

|  |  |
|--|--|
| <b>DEPENDENT PVID</b>  |  |
| <b>APPLICATION</b>   | Contactors for Motors  |
| <b>PRODUCT CATEGORY</b>  | Contactors   |
| <b>PROTECTION</b>  | Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274) |
| <b>ARCING TIME</b>   | 10 ms  |
| <b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>              | Screw connection   |
| <b>SCREWDRIVER SIZE</b>  | 0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver<br>2, Terminal screw, Pozidriv screwdriver  |
| <b>VOLTAGE TYPE</b>  | AC   |
| <b>DEGREE OF PROTECTION</b>                                    | IP20   |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b> | 1  |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>   | 0  |
| <b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>           | 1  |
| <b>NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT</b>    | 0  |
| <b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>             | 0  |
| <b>NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)</b>         | 3  |
| <b>OPERATING TEMPERATURE - MAX</b>                             | 60 °C  |
| <b>OPERATING TEMPERATURE - MIN</b>                             | -25 °C   |
| <b>RATED BREAKING CAPACITY AT 220/230 V</b>                    | 120 A  |
| <b>RATED BREAKING CAPACITY AT 380/400 V</b>                    | 120 A  |
| <b>RATED BREAKING CAPACITY AT 500 V</b>                        | 100 A  |
| <b>RATED BREAKING CAPACITY AT 660/690 V</b>                    | 70 A   |
| <b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50</b>             | 48 V   |

|   |   |
|---|---|
| <b>HZ - MAX</b>   |   |
| <b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b> | 48 V  |
| <b>CONTACT CONFIGURATION</b>                                | 1 NC  |
| <b>DROP-OUT VOLTAGE</b>                                     | AC operated: 0.6 - 0.3 x Uc, AC operated  |
| <b>OVERVOLTAGE CATEGORY</b>                                 | III   |
| <b>DUTY FACTOR</b>  | 100 %   |
| <b>EMITTED INTERFERENCE</b>                                 | According to EN 60947-1   |
| <b>INTERFERENCE IMMUNITY</b>                                | According to EN 60947-1   |
| <b>LIFESPAN, MECHANICAL</b>                                 | 10,000,000 Operations (AC operated)   |
| <b>PICK-UP VOLTAGE</b>                                      | 0.8 - 1.1 V AC x Uc   |
| <b>POWER CONSUMPTION, PICK-UP, 50 HZ</b>                    | 24 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz   |
| <b>SAFE ISOLATION</b>                                       | 400 V AC, Between the contacts, According to EN 61140<br>400 V AC, Between coil and contacts, According to EN 61140   |
| <b>POWER CONSUMPTION, PICK-UP, 60 HZ</b>                    | 30 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz   |
| <b>SCREW SIZE</b>   | M3.5, Terminal screw  |
| <b>POWER CONSUMPTION, SEALING, 50 HZ</b>                    | 1.4 W, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz<br>3.4 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz                     |
| <b>SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)</b> | 10 A, 600 V AC, (UL/CSA)<br>1 A, 250 V DC, (UL/CSA)   |
| <b>SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)</b>  | P300, DC operated (UL/CSA)<br>A600, AC operated (UL/CSA)  |
| <b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>            | 1 x (0.75 - 2.5) mm <sup>2</sup><br>2 x (0.75 - 2,5) mm <sup>2</sup>  |
| <b>SHOCK RESISTANCE</b>                                     | 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms<br>5 g, N/C auxiliary contact, Mechanical, according to |

IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms  
 3.4 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms  
 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms  
 5.7 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms  
 3.4 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms

|  |  |
|--|--|
| <b>TERMINAL CAPACITY (SOLID)</b>                                   | 1 x (0.75 - 4) mm <sup>2</sup><br>2 x (0.75 - 2.5) mm <sup>2</sup> |
| <b>TERMINAL CAPACITY (SOLID/STRANDED AWG)</b>                      | Single 18 - 10, double 18 - 14                                     |
| <b>SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)</b>             | 20 A, Maximum motor rating (UL/CSA)                                |
| <b>TIGHTENING TORQUE</b>   | 1.2 Nm, Screw terminals  |
| <b>RATED INSULATION VOLTAGE (UI)</b>                               | 690 V  |
| <b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947)</b> | 144 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V</b> | 22 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b> | 12 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b> | 12 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V</b>               | 12 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>               | 10 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>        | 7 A  |

|  |        |
|--|--------|
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V</b>   | 7 A    |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V</b>                 | 7 A    |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V</b>                 | 7 A    |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V</b>                 | 6 A    |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V</b>          | 5 A    |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V</b>                 | 20 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V</b>                 | 15 A   |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V</b>                  | 20 A   |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 12 A   |
| <b>RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ</b>                 | 4 kW   |
| <b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>             | 5.5 kW |
| <b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>                 | 7 kW   |
| <b>RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ</b>             | 2 kW   |
| <b>RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ</b>                 | 2.2 kW |
| <b>RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ</b>             | 3 kW   |
| <b>RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ</b>                 | 3.4 kW |
| <b>RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ</b>                 | 3.6 kW |
| <b>RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ</b>                 | 3.5 kW |

|   |   |
|---|---|
| <b>HZ</b>   |   |
| <b>RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ</b>                | 4.4 kW  |
| <b>RATED OPERATIONAL POWER (NEMA)</b>                                   | 7.4 kW  |
| <b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>                       | 690 V   |
| <b>RESISTANCE PER POLE</b>  | 2.5 mΩ  |
| <b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>               | 1.4 W   |
| <b>STRIPPING LENGTH (CONTROL CIRCUIT CABLE)</b>                         | 10 mm   |
| <b>STRIPPING LENGTH (MAIN CABLE)</b>                                    | 10 mm   |
| <b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX</b> | 21 ms   |
| <b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN</b> | 15 ms   |
| <b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX</b> | 18 ms   |
| <b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN</b> | 9 ms  |
| <b>SHORT-CIRCUIT CURRENT RATING (BASIC RATING)</b>                      | 5 kA, 45 A max. fuse, SCCR (UL/CSA)<br>5 kA, 45 A max. CB, SCCR (UL/CSA)                        |
| <b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)</b>               | 100 kA, 45 A CLASS J max. fuse, SCCR (UL/CSA)<br>30 kA, 25 A CLASS RK5 max. fuse, SCCR (UL/CSA) |
| <b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)</b>               | 100 kA, 45 A CLASS J max. fuse, SCCR (UL/CSA)<br>30 kA, 25 A CLASS RK5 max. fuse, SCCR (UL/CSA) |
| <b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V</b>   | 35 A gG/gL  |
| <b>SUITABLE FOR</b>   | Also motors with efficiency class IE3   |

|   |   |
|---|---|
| <b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V</b> | 25 A gG/gL  |
| <b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V</b> | 20 A gG/gL  |
| <b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V</b> | 20 A gG/gL  |
| <b>SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS</b>   | 20 A (480V 60Hz 3phase, 277V 60Hz 1phase)<br>20 A (600V 60Hz 3phase, 347V 60Hz 1phase)  |
| <b>SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING</b>              | 72 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)<br>12 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)  |
| <b>SPECIAL PURPOSE RATING OF ELEVATOR CONTROL</b>                     | 2 HP, 240 V 60 Hz 3-ph, (UL/CSA)<br>2 HP, 200 V 60 Hz 3-ph, (UL/CSA)<br>7.8 A, 200 V 60 Hz 3-ph, (UL/CSA)<br>9 A, 600 V 60 Hz 3-ph, (UL/CSA)<br>6.8 A, 240 V 60 Hz 3-ph, (UL/CSA)<br>7.5 HP, 480 V 60 Hz 3-ph, (UL/CSA)<br>11 A, 480 V 60 Hz 3-ph, (UL/CSA)<br>7.5 HP, 600 V 60 Hz 3-ph, (UL/CSA) |
| <b>SPECIAL PURPOSE RATING OF REFRIGERATION CONTROL (CSA ONLY)</b>     | 10 A, FLA 480 V 60 Hz 3phase; (CSA)<br>10 A, FLA 600 V 60 Hz 3phase; (CSA)<br>60 A, LRA 600 V 60 Hz 3phase; (CSA)<br>60 A, LRA 480 V 60 Hz 3phase; (CSA)  |
| <b>SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING</b>               | 20 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)<br>20 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)  |
| <b>SPECIAL PURPOSE RATING OF TUNGSTEN INCANDESCENT LAMPS</b>          | 14 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)<br>14 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase,   |

