

Eaton 278853

Eaton Moeller series xEffect - FAZ MCB. FAZ, 3-pole, tripping characteristic: B, rated current In: 63 A

PRODUCT NAME	Eaton Moeller series xEffect - FAZ MCB
CATALOG NUMBER	278853
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	0.369 kg
COMPLIANCES	UL CSA09 (with supplementary protector only) RoHS conform
CERTIFICATIONS	CSA (Class No. 3215-30) North America (UL recognized, CSA certified) UL (File No. E177451) CSA-C22.2 No. 235 CSA (File No. 204453) CE marking IEC/EN 60898 UL (Category Control Number QVNU2, QVNU8) IEC/EN 60947-2 UL 1077 EN45545-2 IEC 61373

USED WITH	FAZ Miniature circuit breaker
AMPERAGE RATING	63 A
VOLTAGE RATING	240 V AC / 415 V AC
FEATURES	Additional equipment possible
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to

CHARACTERISTIC CURVE

[eaton-xeffect-faz-mcb-characteristic-curve.jpg](#)

[eaton-mcb-current-xeffect-faz-characteristic-curve.eps](#)

[eaton-mcb-current-xeffect-faz-characteristic-curve-002.eps](#)

[eaton-mcb-tripping-characteristic-xeffect-faz-characteristic-curve-002.eps](#)

[eaton-mcb-xeffect-faz-characteristic-curve.eps](#)

[eaton-mcb-xeffect-faz-characteristic-curve-002.eps](#)

[eaton-mcb-xeffect-faz-wiring-diagram-003.eps](#)

[eaton-xpole-mmc4-6-m-mcb-wiring-diagram-005.jpg](#)

[eaton-xeffect-faz-mcb-dimensions-003.jpg](#)

[eaton-mcb-xeffect-faz-dimensions-003.eps](#)

[eaton-xeffect-faz-mcb-3d-drawing-008.jpg](#)

[eaton-xeffect-faz-mcb-3d-drawing-007.jpg](#)

[eaton-mcb-faz-xeffect-faz-3d-drawing-003.eps](#)

[eaton-xeffect-faz-mcb-3d-drawing.jpg](#)

	be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	45 mm
POLLUTION DEGREE	2
MOUNTING METHOD	Top-hat rail IEC/EN 60715
DEGREE OF PROTECTION	IP20 (IEC) IP40 (when fitted) IP20 UL/CSA Type: -
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	17.2 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
ADMISSIBLE BACK-UP FUSE - MAX	125 A gL/gG
BREAKING CAPACITY	5 kA (UL1077)
BUSBAR MATERIAL THICKNESS	0.8 mm - 2 mm
TERMINAL PROTECTION	Finger and hand touch safe, DGUV VS3, EN 50274
TERMINALS (TOP AND	Twin-purpose terminals

BOTTOM)	
TRIPPING CHARACTERISTIC	B
VOLTAGE RATING (UL CSA 13)	480 Y/277 V AC
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
ENCLOSURE WIDTH	80 mm
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
DIRECTION OF INCOMING SUPPLY	As required
WIDTH IN NUMBER OF MODULAR SPACINGS	3
VOLTAGE RATING (UL)	480Y/277 V
VOLTAGE RATING AT DC	60 V DC (per pole)
VOLTAGE TYPE	AC
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III

NUMBER OF POLES	Three-pole
LIFESPAN, ELECTRICAL	10000 operations
RELEASE CHARACTERISTIC	B
TYPE	• FAZ • Miniature circuit breaker
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	• Branch circuits, not as BCPD • Switchgear for industrial and advanced commercial applications • xEffect - Switchgear for industrial and advanced commercial applications
MOUNTING WIDTH	17.5 mm
SELECTIVITY CLASS	3
MOUNTING WIDTH PER POLE	17.5 mm
NUMBER OF POLES (PROTECTED)	3
NUMBER OF POLES (TOTAL)	3
OPERATIONAL SWITCHING CAPACITY	7.5 kA
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	63 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT	10 kA

400 V	
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	15 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V	15 kA
RATED SWITCHING CAPACITY (IEC/EN 60947- 2)	15 kA
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT	0 W
TERMINAL CAPACITY (CONTROL CABLE)	25 mm ² (1x)
TERMINAL CAPACITY OF SCREW TERMINALS FOR MAIN CABLE	10 mm ² (2x)
POWER LOSS	18.1 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

