

## Eaton 277128

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 11 kW, 1 N/O, 42 V 50 Hz, 48 V 60 Hz, AC operation, Screw terminals DILM25-10(42V50HZ,48V60HZ)

<b>PRODUCT NAME</b>	Eaton Moeller® series DILM contactor
<b>CATALOG NUMBER</b>	277128
<b>PRODUCT LENGTH/DEPTH</b>	97 mm
<b>PRODUCT HEIGHT</b>	85 mm
<b>PRODUCT WIDTH</b>	45 mm
<b>PRODUCT WEIGHT</b>	0.428 kg
<b>CERTIFICATIONS</b>	CSA Certified UL Listed IEC 60947-4-1 EN 60947-4-1 CSA-C22.2 No. 60947-4-1-14 UL IEC/EN 60947 IEC/EN 60947-4-1 CSA CE UL File No.: E29096 UL Category Control No.: NLDX CSA File No.: 012528 VDE 0660 UL 60947-4-1 CSA Class No.: 2411-03, 3211-04
<b>CATALOG NOTES</b>	Contacts according to EN 50012

<b>USED WITH</b>	Can be combined with auxiliary contacts: DILM32-XHI, DILA-XHI(V)
<b>ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT</b>	Screw connection
<b>AMPERAGE RATING</b>	170A
<b>HP RATING - MAX</b>	2, 5/ 7.5, 10, 15, 20 hp (1/3PH @120,240/208,240,480,600 V)
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Full voltage non-reversing small contactor
<b>VOLTAGE RATING</b>	400 V
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO</b>	Meets the product standard's requirements.

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-contactors-switch-dilm-characteristic-curve.eps</a>
	<a href="#">eaton-contactors-switch-dilm-characteristic-curve-002.eps</a>
	<a href="#">IL03407014Z2021_09.pdf</a>
	<a href="#">eaton-contactors-contact-dilm-wiring-diagram.eps</a>
	<a href="#">Eaton Specification Sheet - 277128</a>
	<a href="#">eaton-contactors-dimensions-210t014.eps</a>

<b>ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FREQUENCY RATING</b>	50-60 Hz
<b>OPERATING FREQUENCY</b>	5000 mechanical Operations/h (AC operated)
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No

<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	8000 V AC
<b>UTILIZATION CATEGORY</b>	AC-3: Normal AC induction motors: starting, switch off during running AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-1: Non-inductive or slightly inductive loads, resistance furnaces
<b>CONNECTION</b>	Screw terminals
<b>FRAME SIZE</b>	FS2
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	80 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE</b>	2 HP
<b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE</b>	7.5 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE</b>	5 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE</b>	10 HP
<b>ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE</b>	15 HP
<b>ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE</b>	20 HP
<b>CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)</b>	90 A
<b>CONVENTIONAL</b>	36 A

<b>THERMAL CURRENT ITH (3-POLE, ENCLOSED)</b>	
<b>CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)</b>	42 A
<b>CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1- POLE, OPEN)</b>	100 A
<b>EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID</b>	4.2 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID</b>	1.4 W
<b>APPLICATION</b>	Contactors for Motors
<b>PRODUCT CATEGORY</b>	Contactors
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
<b>TERMINALS</b>	Screw terminals
<b>ARCING TIME</b>	10 ms
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>SCREWDRIVER SIZE</b>	0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
<b>VOLTAGE TYPE</b>	AC
<b>DEGREE OF PROTECTION</b>	IP00
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT</b>	0
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF MAIN</b>	3

<b>CONTACTS (NORMALLY OPEN CONTACT)</b>	
<b>OPERATING TEMPERATURE - MAX</b>	60 °C
<b>OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>RATED BREAKING CAPACITY AT 220/230 V</b>	250 A
<b>RATED BREAKING CAPACITY AT 380/400 V</b>	250 A
<b>RATED BREAKING CAPACITY AT 500 V</b>	250 A
<b>RATED BREAKING CAPACITY AT 660/690 V</b>	150 A
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX</b>	42 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b>	42 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX</b>	48 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN</b>	48 V
<b>COIL VOLTAGE</b>	28-42 Vac, 50/60 Hz
<b>CONTACT CONFIGURATION</b>	1 NO
<b>CONTINUOUS AMPERE RATING</b>	40 A
<b>DROP-OUT VOLTAGE</b>	AC operated: 0.6 - 0.3 x UC, AC operated
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DUTY FACTOR</b>	100 %
<b>NUMBER OF CONTACTS</b>	1 NO
<b>EMITTED INTERFERENCE</b>	According to EN 60947-1
<b>OPERATION</b>	Reversing
<b>INTERFERENCE IMMUNITY</b>	According to EN 60947-1
<b>LIFESPAN, MECHANICAL</b>	10,000,000 Operations (AC operated)
<b>PICK-UP VOLTAGE</b>	0.8 - 1.1 V AC x Uc
<b>POWER CONSUMPTION, PICK-UP, 50 HZ</b>	52 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz

<b>SAFE ISOLATION</b>	440 V AC, Between the contacts, According to EN 61140 440 V AC, Between coil and contacts, According to EN 61140
<b>POWER CONSUMPTION, PICK-UP, 60 HZ</b>	67 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz
<b>SCREW SIZE</b>	M5, Terminal screw, Main cables M3.5, Terminal screw, Control circuit cables
<b>POWER CONSUMPTION, SEALING, 50 HZ</b>	2.1 W, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz 7.1 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz
<b>POWER CONSUMPTION, SEALING, 60 HZ</b>	8.7 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz 2.1 W, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz
<b>TERMINAL CAPACITY (STRANDED)</b>	1 x 16 mm <sup>2</sup> , Main cables
<b>SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)</b>	10 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
<b>SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)</b>	A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)
<b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>	1 x (0.75 - 16) mm <sup>2</sup> , Main cables 2 x (0.75 - 10) mm <sup>2</sup> , Main cables 1 x (0.75 - 2.5) mm <sup>2</sup> , Control circuit cables 2 x (0.75 - 2.5) mm <sup>2</sup> , Control circuit cables
<b>SHOCK RESISTANCE</b>	5.3 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact,

	<p>Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 6.9 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 3.5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms</p>
<b>TERMINAL CAPACITY (SOLID)</b>	<p>1 x (0.75 - 16) mm<sup>2</sup>, Main cables  1 x (0.75 - 4) mm<sup>2</sup>, Control circuit cables  2 x (0.75 - 10) mm<sup>2</sup>, Main cables  2 x (0.75 - 2.5) mm<sup>2</sup>, Control circuit cables</p>
<b>TERMINAL CAPACITY (SOLID/STRANDED AWG)</b>	<p>Single 18 - 6, double 18 - 8, Main cables  18 - 14, Control circuit cables</p>
<b>SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)</b>	40 A, Maximum motor rating (UL/CSA)
<b>POWER CONSUMPTION</b>	11 kW
<b>TIGHTENING TORQUE</b>	<p>1.2 Nm, Screw terminals, Control circuit cables  3.2 Nm, Screw terminals, Main cables</p>
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	0 V
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947)</b>	350 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V</b>	45 A



<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>	25 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	25 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V</b>	25 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>	25 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>	15 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V</b>	13 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V</b>	13 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V</b>	13 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V</b>	13 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V</b>	10 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V</b>	40 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	25 A
<b>RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ</b>	8.5 kW
<b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>	11 kW
<b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50</b>	14.5 kW

<b>HZ</b>	
<b>RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ</b>	3.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ</b>	4 kW
<b>RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ</b>	6 kW
<b>RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ</b>	6.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ</b>	7 kW
<b>RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ</b>	8 kW
<b>RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ</b>	8.5 kW
<b>RATED OPERATIONAL POWER (NEMA)</b>	11 kW
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	690 V
<b>RESISTANCE PER POLE</b>	2.7 mΩ
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	2.1 W
<b>STRIPPING LENGTH (CONTROL CIRCUIT CABLE)</b>	10 mm
<b>STRIPPING LENGTH (MAIN CABLE)</b>	10 mm
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX</b>	22 ms
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN</b>	16 ms
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX</b>	14 ms
<b>SWITCHING TIME (AC</b>	8 ms

<b>OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN</b>	
<b>SHORT-CIRCUIT CURRENT RATING (BASIC RATING)</b>	5 kA, SCCR (UL/CSA) 125 A, max. CB, SCCR (UL/CSA) 125 A, max. Fuse, SCCR (UL/CSA)
<b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)</b>	10/65 kA, CB, SCCR (UL/CSA) 50/32 A, max. CB, SCCR (UL/CSA) 10/100 kA, Fuse, SCCR (UL/CSA) 125/70 A, Class J, max. Fuse, SCCR (UL/CSA)
<b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)</b>	10/22 kA, CB, SCCR (UL/CSA) 50/32 A, max. CB, SCCR (UL/CSA) 10/100 kA, Fuse, SCCR (UL/CSA) 125/100 A, Class J, max. Fuse, SCCR (UL/CSA)
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V</b>	100 A gG/gL
<b>SUITABLE FOR</b>	Also motors with efficiency class IE3
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V</b>	50 A gG/gL
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V</b>	35 A gG/gL
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V</b>	35 A gG/gL
<b>SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS</b>	40 A (600V 60Hz 3phase, 347V 60Hz 1phase) 40 A (480V 60Hz 3phase, 277V 60Hz 1phase)
<b>SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING</b>	25 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 150 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)

<b>SPECIAL PURPOSE RATING OF ELEVATOR CONTROL</b>	15.2 A, 240 V 60 Hz 3-ph, (UL/CSA) 11 A, 200 V 60 Hz 3-ph, (UL/CSA) 5 HP, 240 V 60 Hz 3-ph, (UL/CSA) 10 HP, 480 V 60 Hz 3-ph, (UL/CSA) 3 HP, 200 V 60 Hz 3-ph, (UL/CSA) 15 HP, 600 V 60 Hz 3-ph, (UL/CSA) 17 A, 600 V 60 Hz 3-ph, (UL/CSA) 14 A, 480 V 60 Hz 3-ph, (UL/CSA)
<b>SPECIAL PURPOSE RATING OF REFRIGERATION CONTROL (CSA ONLY)</b>	40 A, FLA 480 V 60 Hz 3phase; (CSA) 240 A, LRA 480 V 60 Hz 3phase; (CSA) 180 A, LRA 600 V 60 Hz 3phase; (CSA) 30 A, FLA 600 V 60 Hz 3phase; (CSA)
<b>SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING</b>	40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
<b>SPECIAL PURPOSE RATING OF TUNGSTEN INCANDESCENT LAMPS</b>	40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
<b>OPERATING TEMPERATURE</b>	-25° to 60°C
<b>CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)</b>	45 A
<b>CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)</b>	43 A
<b>CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)</b>	40 A
<b>RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ</b>	15.5 kW
<b>RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ</b>	17.5 kW

<b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>	14 kW
<b>ACTUATING VOLTAGE</b>	42 V 50 Hz, 48 V 60 Hz
<b>ALTITUDE</b>	Max. 2000 m
<b>OPERATING VOLTAGE AT AC, 50 HZ - MIN</b>	24 V
<b>OPERATING VOLTAGE AT AC, 50 HZ - MAX</b>	690 V
<b>OPERATING VOLTAGE AT AC, 60 HZ - MIN</b>	24 V
<b>OPERATING VOLTAGE AT AC, 60 HZ - MAX</b>	690 V

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

