

Eaton 279061

Eaton Moeller series xEffect - FAZ MCB. FAZ, 4 pole, tripping characteristic: C, rated current In: 16 A

PRODUCT NAME	Eaton Moeller series xEffect - FAZ MCB
CATALOG NUMBER	279061
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	72 mm
PRODUCT WEIGHT	0.445 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60898 IEC/EN 60947-2 EN45545-2 IEC 61373

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	45 mm
POLLUTION DEGREE	2
MOUNTING METHOD	Top-hat rail IEC/EN 60715
DEGREE OF PROTECTION	IP20 IP40 (when fitted)
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	8.8 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
ADMISSIBLE BACK-UP FUSE - MAX	125 A gL/gG
BREAKING CAPACITY	10 kA (UL1077)
BUSBAR MATERIAL THICKNESS	0.8 mm - 2 mm
TERMINAL PROTECTION	Finger and hand touch safe, DGUV VS3, EN 50274
TERMINALS (TOP AND	Twin-purpose terminals

BOTTOM)	
TRIPPING CHARACTERISTIC	C
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
ENCLOSURE WIDTH	80 mm
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
DIRECTION OF INCOMING SUPPLY	As required
VOLTAGE RATING (IEC/EN 60898-1)	415 VAC
WIDTH IN NUMBER OF MODULAR SPACINGS	4
VOLTAGE RATING (UL)	480Y/277 V
VOLTAGE RATING AT DC	60 V DC (per pole)
VOLTAGE TYPE	AC
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III

NUMBER OF POLES	Four-pole
LIFESPAN, ELECTRICAL	10000 operations
RELEASE CHARACTERISTIC	C
TYPE	• FAZ • Miniature circuit breaker
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	• Switchgear for industrial and advanced commercial applications • xEffect - Switchgear for industrial and advanced commercial applications
MOUNTING WIDTH	17.5 mm
SELECTIVITY CLASS	3
MOUNTING WIDTH PER POLE	17.5 mm
NUMBER OF POLES (PROTECTED)	4
NUMBER OF POLES (TOTAL)	4
OPERATIONAL SWITCHING CAPACITY	7.5 kA
OPERATIONAL VOLTAGE (IEC/EN 60947-2) - MAX	440 VAC
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	16 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICS	7.5 kA
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60947-	7.5 kA

2) - ICS

**RATED SHORT-CIRCUIT
BREAKING CAPACITY
(IEC/EN 60898-1) - ICN AT
230 V**

10 kA

**RATED SHORT-CIRCUIT
BREAKING CAPACITY
(IEC/EN 60898-1)- ICN AT
400 V**

10 kA

**RATED SHORT-CIRCUIT
BREAKING CAPACITY (IEC
60947-2)- ICU AT 230 V**

15 kA

**RATED SHORT-CIRCUIT
BREAKING CAPACITY (IEC
60947-2)- ICU AT 400 V**

15 kA

**RATED SWITCHING
CAPACITY (IEC/EN 60898-
1)**

10 kA

**RATED SWITCHING
CAPACITY (IEC/EN 60947-
2)**

15 kA

**RATED SWITCHING
CAPACITY (IEC/EN 60947-
2) AT MAX VOLTAGE
RATING**

10 kA

**STATIC HEAT
DISSIPATION, NON-
CURRENT-DEPENDENT**

0 W

**TERMINAL CAPACITY
(CONTROL CABLE)**

25 mm² (1x)

**TERMINAL CAPACITY OF
SCREW TERMINALS FOR
MAIN CABLE**

10 mm² (2x)

POWER LOSS

7.5 W

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

