



## Eaton 279154

Eaton Moeller series xEffect - FAZ-PN MCB.  
FAZ-PN, 1-pole+N, tripping characteristic: C,  
rated current In: 2 A

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xEffect - FAZ-PN MCB
<b>CATALOG NUMBER</b>	279154
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	75.5 mm
<b>PRODUCT WIDTH</b>	17.5 mm
<b>PRODUCT WEIGHT</b>	0.115 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 60898 EN45545-2 IEC 61373



Powering Business Worldwide

<b>USED WITH</b>	FAZ-PN Miniature circuit breaker
<b>AMPERAGE RATING</b>	2 A
<b>VOLTAGE RATING</b>	240 V AC / 415 V AC
<b>FEATURES</b>	Concurrently switching N-neutral Additional equipment possible
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.

□□□□□	<a href="#">eaton-rccb-rcbo-g9-il019140zu.pdf</a>
□□□	<a href="#">eaton-xpole-mmc4-6-mcb-wiring-diagram.jpg</a>
□□□□	<a href="#">eaton-mcb-xeffect-faz-wiring-diagram-005.eps</a>
□□□□	<a href="#">eaton-xeffect-faz-mcb-catalog-ca003028en-en-us.pdf</a>
□□	<a href="#">eaton-xeffect-faz-mcb-dimensions-002.jpg</a> <a href="#">eaton-mcb-xeffect-faz-pn-dimensions.eps</a> <a href="#">eaton-mcb-faz-xeffect-faz-3d-drawing-002.eps</a>
□□□□□□	<a href="#">eaton-maximum-cable-lengths-for-eatons-protective-devices-brochure-br034006en-en-us.pdf</a>

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FRAME</b>	45 mm
<b>POLLUTION DEGREE</b>	2
<b>MOUNTING METHOD</b>	Top-hat rail IEC/EN 60715
<b>DEGREE OF PROTECTION</b>	IP20 IP40 (when fitted)
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>ADMISSIBLE BACK-UP FUSE - MAX</b>	100 A gL/gG
<b>TERMINAL PROTECTION</b>	Finger and hand touch safe, DGUV VS3, EN 50274
<b>TERMINALS (TOP AND BOTTOM)</b>	Twin-purpose terminals
<b>TRIPPING CHARACTERISTIC</b>	C
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	25 mm <sup>2</sup>

<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CURRENT LIMITING CLASS</b>	3
<b>ENCLOSURE WIDTH</b>	80 mm
<b>FREQUENCY RATING - MAX</b>	60 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	1
<b>VOLTAGE RATING AT DC</b>	60 V DC (per pole)
<b>VOLTAGE TYPE</b>	AC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Single-pole + N
<b>LIFESPAN, ELECTRICAL</b>	4000 operations
<b>RELEASE CHARACTERISTIC</b>	C
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• FAZ-PN</li> <li>• Miniature circuit breaker</li> </ul>
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Switchgear for industrial and advanced commercial applications</li> <li>• xEffect - Switchgear for industrial and advanced commercial applications</li> </ul>
<b>MOUNTING WIDTH</b>	17.5 mm
<b>SELECTIVITY CLASS</b>	3
<b>MOUNTING WIDTH PER POLE</b>	17.5 mm

