



## Eaton 280MMT

Eaton Bussmann series high speed British standard fuse, Double barrel, 280A, 690 VAC/350 VDC (IEC), 700 VAC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 40 kA DC at 350 VDC (IEC)

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed british standard fuse
<b>CATALOG NUMBER</b>	280MMT
<b>UPC</b>	051712833394
<b>PRODUCT LENGTH/DEPTH</b>	110 mm
<b>PRODUCT HEIGHT</b>	83 mm
<b>PRODUCT WIDTH</b>	39 mm
<b>PRODUCT WEIGHT</b>	478 g
<b>COMPLIANCES</b>	RoHS Compliant CE Marked

□□□□	
AMPERAGE RATING	280 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	350 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	85 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	47000
WATT LOSSES	47 W
FUSE SHAPE	Center dual barrel bolted tags
PRE ARC (I2T)	6600
COLOR	None
INTERRUPT RATING	200 kA RMS Sym (IEC/UL), 40 kA at 350 Vdc (IEC)
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	MMT
SUITABLE FOR	MC-700 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250923en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

