

Eaton 281195

Eaton Moeller® series DILM Paralleling link,
for DILM40-65

PRODUCT NAME	Eaton Moeller® series DILM paralleling link
CATALOG NUMBER	281195
PRODUCT LENGTH/DEPTH	77 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	47 mm
PRODUCT WEIGHT	0.24 kg
CERTIFICATIONS	CSA File No.: 012528 UL 508 UL File No.: E29096 IEC/EN 60947-4-1 UL UL Category Control No.: NLDX CE CSA Class No.: 3211-03 CSA-C22.2 No. 14-05 CSA
CATALOG NOTES	AC1 current carrying capacity of the open contactor increases by a factor of 2.5

10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.

MCAD MODEL	dil_m65_xp1.stp
	eaton-contactors-dilm-paralleling-link-wiring-diagram-002.eps
	eaton-contactors-dilm-paralleling-link-3d-drawing.eps

10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ACCESSORY/SPARE PART TYPE	Connecting bridge
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)	180 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	1.5 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.5 W
TERMINAL CAPACITY	1 x (16 - 120) mm ² , stranded, Main cables 1 x (16 - 120) mm ² , flexible with ferrule, Main cables 16 mm ² , solid
SCREW SIZE	5 mm AF, Hexagon socket-head spanner, Terminal screw
TIGHTENING TORQUE	14 Nm, Screw terminal
RATED OPERATIONAL	215 A

CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
PROTECTION	Protected against accidental contact in accordance to VDE 0106 part 100
PRODUCT CATEGORY	Accessories

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

