



□□□□□

## Eaton 285347

Eaton xComfort BF LV systems Final  
Distribution Boards. Complete surface-  
mounted flat distribution board, white, 24  
SU per row, 5 rows, type P

□□□□

<b>PRODUCT NAME</b>	Eaton xComfort BF small distribution board
<b>CATALOG NUMBER</b>	285347
<b>PRODUCT LENGTH/DEPTH</b>	915 mm
<b>PRODUCT HEIGHT</b>	145 mm
<b>PRODUCT WIDTH</b>	570 mm
<b>PRODUCT WEIGHT</b>	14.6 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 61439-1 IEC/EN 62208 IEC/EN 61439-3



Powering Business Worldwide

<b>USED WITH</b>	Installation distribution board BF flat distribution board Basic device
<b>SPECIAL FEATURES</b>	IP30 Protection Class I Steel sheet enclosure white (RAL 9016)
<b>TYPE</b>	Basic device BF flat DBO Installation distribution boards
<b>FEATURES</b>	EMC-version Earthing terminal block Neutral terminal block
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility.
<b>10.13 MECHANICAL FUNCTION</b>	Meets the product standard's requirements.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Not relevant to indoor installations.
<b>10.2.5 LIFTING</b>	Does not apply to enclosures without lifting aids.
<b>10.2.6 MECHANICAL IMPACT</b>	IK07
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF</b>	IP30

□□□□	<a href="#">eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf</a>
□□	<a href="#">eaton-xcomfort-bf-lv-systems-dimensions.eps</a>

<b>ASSEMBLIES</b>	
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Is the panel builder's responsibility.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	< 0.1 $\Omega$ ; meets the product standard's requirements.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Is the panel builder's responsibility.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Ui = 415 V AC
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Does not apply to basic enclosures as defined in EN 62208.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Does not apply to metal enclosures.
<b>FITTED WITH:</b>	Door with three-point turn-lock Enclosure DIN rail mounting frame Front plates Neutral-/protective conductor terminal Cable gland plate inserts (top)
<b>ENCLOSURE MATERIAL</b>	Steel
<b>BUILT-IN HEIGHT</b>	145 mm
<b>BUILT-IN WIDTH</b>	570 mm
<b>CABLE ENTRY POSTION</b>	Cable entries on top and bottom
<b>TERMINAL TYPE</b>	Screw terminals
<b>BUILT-IN DEPTH</b>	915 mm
<b>HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)</b>	59 W
<b>HEAT DISS. AMBIENT 35°C DELTA T: 20°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)</b>	53 W
<b>HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)</b>	56 W
<b>CLOSURE TYPE</b>	Other

<b>COVER/DOOR COLOR</b>	White
<b>COVER/DOOR MODEL</b>	Closed
<b>COVER/DOOR TYPE</b>	Door Single
<b>RAL-NUMBER</b>	9016
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	24
<b>AMBIENT OPERATING TEMPERATURE DETAILS</b>	-5 °C - 40 °C
<b>APPLICATION</b>	Indoor (installation site)
<b>VOLTAGE RATING AT AC</b>	415 V AC
<b>COLOR</b>	Traffic white (RAL 9016) White
<b>NUMBER OF ROWS</b>	5
<b>FREQUENCY RATING OF CONTACTS</b>	50 Hz / 60 Hz
<b>MODULE RACK TYPE</b>	Rail frame
<b>DEGREE OF PROTECTION</b>	IK07 (impact resistance) IP30
<b>NUMBER OF MODULE SPACE UNITS PER ROW</b>	24
<b>PROTECTION CLASS</b>	I (earthed)
<b>PROTECTIVE SHROUDING MATERIAL</b>	Metal
<b>FUNCTIONS</b>	Basic device Sealable
<b>MATERIAL</b>	Sheet steel, powder-coated
<b>MOUNTING METHOD</b>	Surface mounting DIN-rail Surface mounted (plaster)
<b>HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)</b>	118 W
<b>HEAT DISS. AMBIENT 35°C DELTA T: 35°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)</b>	107 W
<b>HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)</b>	112 W
<b>INTERNAL DEPTH</b>	131 mm
<b>PE AND N TERMINAL NUMBER AND CROSS SECTION</b>	PE: 2 x 25 mm <sup>2</sup> + 58 x 16 mm <sup>2</sup> N: 2 x 25 mm <sup>2</sup> + 58 x 16 mm <sup>2</sup>
<b>NUMBER OF OPENINGS FOR SOCKET OUTLETS</b>	0

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

